

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0347739140

Status:


Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

Stac64 Hybrid Header, 14 Circuits, Right-Angle, Polarization A, Mylar Pin Alignment Plate, Black, Tube



Series image - Reference only

Documents:	
Drawing (PDF)	Application Specification 347290200-AS-CH-000 (PDF)
3D Model	Brochure (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-34969-100-001 (PDF)	

General	
Product Family	PCB Headers
Series	34773
Application	Automotive, Power, Wire-to-Board
Comments	Current is dependent on connector size, ambient temperature, blade size and related factors. 2.80mm – 30.0A; 0.64mm - 6.0A. Polarization A
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Packaging Alternative	347730140
Product Name	Stac64
UPC	884982910553
Physical	
Breakaway	No
Circuits (Loaded)	14
Circuits (maximum)	14
Circuits Detail	10 x 0.64 and 4 x 2.8
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	10.313/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tube
Pitch - Mating Interface	2.54mm, 5.25mm
Pitch - Termination Interface	2.54mm, 5.25mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	N/A

EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
34773 Series

Mates With
Stac64 Hybrid Receptacle Connector [34969](#)

Electrical

Current - Maximum per Contact	30.0A, 6.0A
Voltage - Maximum	500V DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	347290200-AS-CH-000
Product Specification	PS-34969-100-001
Sales Drawing	SD-34708-300-001, SD-34708-400-001, SD-34773-010-001, SD-34997-200-001, SD-34997-300-001, SD-34997-400-001

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

34773-9140