

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0348033212

Status:

Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

CTX64 Female Terminal, Tin, L-Grip, D-Wind, Left Payoff, SAE 20



Series image - Reference only

Documents:

Drawing (PDF)	Application Specification AS-560065-001-CH-001 (PDF)
Product Specification PS-502306-001-001 (PDF)	Application Specification AS-560065-001-FR-001 (PDF)
Application Specification AS-502306-002-001 (PDF)	Packaging Specification PK-31301-053-001 (PDF)
Application Specification AS-502306-002-CH-001 (PDF)	Brochure (PDF)
Application Specification AS-502306-002-FR-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-560065-001-001 (PDF)	

General

Product Family	Crimp Terminals
Series	34803
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Product Name	CTX64
UPC	887191519296

Physical

Gender	Female
Grip Code	L
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.124/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40 to 1.90mm
Wire Size AWG	20
Wire Size mm²	0.50-0.85

Electrical

Current - Maximum per Contact	See Receptacle Product Spec.
Voltage - Maximum	14V DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-502306-002-001, AS-502306-002-CH-001, AS-502306-002-FR-001, AS-560065-001-001, AS-560065-001-CH-001, AS-560065-001-FR-001
Packaging Specification	PK-31301-053-001
Product Specification	PS-502306-001-001
Sales Drawing	SD-31301-053-001, SD-34803-002-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
reaction mass of
2-ethylhexyl 10-
ethyl-4,4-dioct
Methylhexahydrophthalic
anhydride
Perfluorononan-1-
oic acid
(2,2,3,3,4,4,5,5,6,6,7
Dioctyltin dilaurate,
stannane, dioctyl-,
bis(co
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
Nonadecafluorodecanoic
acid (PFDA) and its
sodiu
Zirconia
Aluminosilicate
Refractory Ceramic
Fibr
Aluminosilicate
Refractory Ceramic
Fibres
n-pentyl-
isopentylphthalate
1,2-
Benzenedicarboxylic
acid, dipentyl ester, br
1,2-
Benzenedicarboxylic
acid, dihexyl ester,
bra
Terphenyl,
hydrogenated
2-(2H-Benzotriazol-2-
yl)-4,6-
ditertpentylphenol

China RoHS

2-ethylhexyl 10-ethyl-4,4-dioctyl-7-oxo-8-oxa-3, Disodium-octaborate 1,3-Propanesultone 1,2- Benzenedicarboxylic acid, bis(3-methylbutyl) Phenanthrene Dicyclohexyl-phthalate 4-aminoazobenzene Fatty Acids, C16-18, Lead Salts Cyanamide, lead(2+) salt (1:1) Lead titanium zirconium oxide Dioxobis(stearato)trilead Tetralead-trioxide-sulphate Trilead-dioxide-phosphonate Pentalead-tetraoxide-sulphate Lead-titanium-trioxide Diboron-trioxide 1,2- Benzenedicarboxylic acid, bis(2-methoxyethyl Pentazinc-chromate-octahydroxide Potassium hydroxyoctaoxodizincatedichromate Boric acid, disodium salt, hydrate

Halogen-Free Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[34803](#) Series

Use With

[34729](#) 2.54mm Pitch Stac64 Right Angle Receptacle

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

Hand Crimp Tool for [638193800](#)
CTX64 Receptacle
Terminal, 0.50, 0.75,
0.85mm² and 20
AWG
FineAdjust Applicator[639032700](#)
for CTX64 Mat
Seal Receptacle
Terminals, for Wire
Process Use Only

This document was generated on 10/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[34803-3212](#) [34803-3212 \(Mouser Reel\)](#) [34803-3212 \(Cut Strip\)](#) [34803-3212 \(Loose Piece\)](#)