

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0513531800

Status:


Active

Overview:

MicroClasp Wire-to-Board System

Description:

2.00mm Pitch MicroClasp Wire-to-Board Receptacle Housing, Positive Lock, Dual Row, 18 Circuits, White



Documents:	
3D Model	Product Specification PS-51353-010-001 (PDF)
3D Model (PDF)	Application Specification 561340000-AS-000 (PDF)
Drawing (PDF)	Packaging Specification SPK-51353-001-001 (PDF)
Product Specification PS-51353-003-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	Crimp Housings
Series	51353
Application	Signal, Wire-to-Board
Overview	MicroClasp Wire-to-Board System
Product Name	MicroClasp
UPC	800756611136
Physical	
Circuits (maximum)	18
Color - Resin	White
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	882.000/mg
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C
Material Info	
Reference - Drawing Numbers	
Application Specification	561340000-AS-000
Packaging Specification	SPK-51353-001-001
Product Specification	PS-51353-003-001, PS-51353-010-001
Sales Drawing	SD-51353-002-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

51353 Series

Mates With

MicroClasp Vertical Header [501844](#)
 MicroClasp Vertical Header with Kinked PC Tails [55917](#)
 MicroClasp Right Angle Header [55959](#)

Use With

MicroClasp TPA Retainer [500638](#)
 Crimp Terminal [56134](#)
 MicroClasp Pre-Crimped Leads [797581001](#) , [797581002](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[51353-1800](#)