

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0351810200](#)
Status: **Active**
Overview: [VersaBlade Wire-to-Wire Connector System](#)
Description: VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Type A, Natural

Documents:

3D Model	Packaging Specification 351810200-100 (PDF)
3D Model (PDF)	Datasheet (PDF)
Drawing (PDF)	Brochure (PDF)
Product Specification PS-35182-003-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	35181
Application	Power, Wire-to-Wire
Brochure Order No	987651-4231
Datasheet Order No	987651-3631
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
UPC	800754376051


Physical

Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	1.566/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	8.00mm
Pitch - Termination Interface	8.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

Material Info

Reference - Drawing Numbers

Packaging Specification	351810200-100
Product Specification	PS-35182-003-001
Sales Drawing	SD-35181-020X



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[35181](#) Series

Mates With

VersaBlade Multi-Module 2-2 and 2-2-2
Receptacle Housings [35180](#)

Use With

VersaBlade Crimp Terminals [35746](#)

VersaBlade TPA [351820190](#) ,
[351820192](#) , [351820193](#) , [351820194](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[35181-0200](#)