

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0354076702](#)
Status: **Active**
Description: 2.28mm Sealed Terminal, Female, 0.30-0.50mm² AVSS, 0.25mm Material Thickness, Pre-Tin Plated

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-35407-003-001 \(PDF\)](#)
[Product Specification PS-35408-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [35407](#)
 Application Power, Wire-to-Board
 Crimp Quality Equipment Yes
 Product Name N/A
 UPC 800756627809


Physical

Gender Female
 Material - Metal High Performance Alloy (HPA)
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.293/g
 Packaging Type Reel
 Plating min - Mating 0.813µm
 Plating min - Termination 0.813µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.90mm max.
 Wire Size AWG 20, 22
 Wire Size mm² N/A

Material Info

Reference - Drawing Numbers

Crimp Specification CS-35407-6702-001
 Packaging Specification PK-35407-003-001
 Product Specification PS-35408-001-001
 Sales Drawing SD-35407-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2021)4569-DC (8
 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[35407](#) Series

Mates With

[35420](#)

Use With

[35825](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for 2.28mm (.090") Sealed Receptacle Terminals	638257600

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[35407-6702](#)