

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0354076802](#)
Status: **Active**
Description: 2.28mm Sealed Terminal, Female, 0.85-1.25mm² AVSS, 0.25mm Material Thickness, Pre-Tin Plated, Reel


Documents:
[Drawing \(PDF\)](#) [Packaging Specification PK-35407-003-001 \(PDF\)](#)
[Product Specification PS-35519-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Terminals
Series	35407
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Product Name	N/A
UPC	756054240014
Physical	
Gender	Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.293/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.90mm max.
Wire Size AWG	16, 18
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers

Crimp Specification	CS-35407-6702-001
Packaging Specification	PK-35407-003-001
Product Specification	PS-35519-001-001
Sales Drawing	SD-35407-001



Series image - Reference only

EU ELV Compliant	
EU RoHS Compliant REACH SVHC Not Contained Per - ED/71/2019 (16 July 2019) Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
	Not Relevant Compliant Not Contained

Search Parts in this Series
[35407](#) Series

Mates With
[35420](#)

Use With
[35825](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool for 2.28mm (.090") Sealed Receptacle Terminal	638257700
FineAdjust for 2.30mm (.090")	639027100

This document was generated on 11/21/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[35407-6802 \(Loose Piece\)](#) [35407-6802 \(Mouser Reel\)](#) [35407-6802 \(Cut Strip\)](#)