

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0621002200

Status:

Active

Overview:

Application Tooling

Description:

Manual Press with IDT Ribbon Cable Tool Kit

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207125
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Arbor Press
UPC	884982115606
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

TM-621002200-001



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207125 Series

Application Tooling Description	FAQ Product #
Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 10 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	875681063
Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 10 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	875681064
Milli-Grid Cable-to-Board Receptacle,	875681073

Milli-Grid Cable-to-Board Receptacle,
 Dual Row, IDT,
 Lead-Free, 10
 Circuits, 0.76μm
 Gold (Au) Selective
 Plating, without
 Center Polarization
 Key, with Locking
 Friction Ramp

Milli-Grid Cable-to-
 Board Receptacle,
 Dual Row, IDT,
 Lead-Free, 12
 Circuits, 0.38μm
 Gold (Au) Selective
 Plating, without
 Center Polarization
 Key and Locking
 Friction Ramp

Milli-Grid Cable-to-Board Receptacle,
 Dual Row, IDT,
 Lead-Free, 12
 Circuits, 0.76µm
 Gold (Au) Selective
 Plating, without
 Center Polarization
 Key and Locking
 Friction Ramp

Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 12 Circuits, 0.38μm Gold (Au) Selective Plating, without Center Polarization Key, with Locking Friction Ramp

Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 12 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key, with Locking Friction Ramp

Milli-Grid Cable-to-Board Receptacle,
Dual Row, IDT,
Lead-Free, 14
Circuits, 0.38μm
Gold (Au) Selective
Plating, with Center

Polarization Key, without Locking Friction Ramp	
Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 14 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875681444</u>
Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 14 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875681463</u>
Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 14 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875681464</u>
MGrid IDT Rec W/ LRmp .38AuLF 14Ckt	<u>875681483</u>
MGrid IDT Rec W/ LRmp .76AuLF 14Ckt	<u>875681484</u>
Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 14 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875681493</u>
Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 14 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875681494</u>
Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 16 Circuits, 0.38µm Gold (Au) Selective	<u>875681643</u>

	Plating, with Center Polarization Key, without Locking Friction Ramp Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 16 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 16 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 16 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp MGrid IDT Rec W/ LRmp .38AuLF 16Ckt MGrid IDT Rec W/ LRmp .76AuLF 16Ckt Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 16 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 16 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 20 Circuits, 0.38µm	875681644 875681663 875681664 875681683 875681684 875681693 875681694 875682043
--	---	--

Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	
Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 20 Circuits, 0.76μm	<u>875682044</u>
Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	
Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 20 Circuits, 0.38μm	<u>875682063</u>
Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	
Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 20 Circuits, 0.76μm	<u>875682064</u>
Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	
MGrid IDT Rec W/ LRmp .38AuLF 20Ckt	<u>875682083</u>
MGrid IDT Rec W/ LRmp .76AuLF 20Ckt	<u>875682084</u>
Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 20 Circuits, 0.38μm	<u>875682093</u>
Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	
Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 20 Circuits, 0.76μm	<u>875682094</u>
Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	
Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 22	<u>875682243</u>

Milli-Grid Cable-to-Board Receptacle,
Dual Row, IDT,
Lead-Free, 22

Milli-Grid Cable-to-Board Receptacle,
Dual Row, IDT,
Lead-Free, 22

Milli-Grid Cable-to-Board Receptacle,
Dual Row, IDT,
Lead-Free, 22

MGrid IDT Rec W/ 875682283
LRmp .38AuLF
22Ckt
MGrid IDT Rec W/ 875682284

Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free ?? 875682293

Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free 22 875682294

Ramp
Milli-Grid Cable-to-
Board Receptacle,
Dual Row, IDT, 875682443

Milli-Grid Cable-to-
Board Receptacle,
Dual Row, IDT,
Lead-Free, 24
Circuits, 0.76µm
Gold (Au) Selective
Plating, with Center
Polarization Key,
without Locking
Friction Ramp

Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 24 Circuits, 0.76μm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp

MGrid IDT Rec W/ 875682484
LRmp .76AuLF
24Ckt

Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 24 Circuits, 0.76μm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp

Milli-Grid Cable-to-
Board Receptacle,
Dual Row, IDT,
Lead-Free, 26
Circuits, 0.76μm
Gold (Au) Selective
Plating, with Center
Polarization Key,
without Locking
Friction Ramp

Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 26 Circuits, 0.38μm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp

Milli-Grid Cable-to-
Board Receptacle,
Dual Row, IDT,
Lead-Free, 26
Circuits, 0.76µm
Gold (Au) Selective
Plating, without
Center Polarization
Key and Locking
Friction Ramp

MGrid IDT Rec W/ 875682683
LRmp .38AuLF
26Ckt

MGrid IDT Rec W/ 875682684
LRmp .76AuLF
26Ckt

Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 26 Circuits, 0.38μm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp

Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 26 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp

	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 30 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875683043</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 30 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875683044</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 30 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875683063</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 30 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875683064</u>
	MGrid IDT Rec W/ LRmp .38AuLF 30Ckt	<u>875683083</u>
	MGrid IDT Rec W/ LRmp .76AuLF 30Ckt	<u>875683084</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 30 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875683093</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 30 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key	<u>875683094</u>

	and Locking Friction Ramp	
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 34 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875683443</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 34 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875683444</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 34 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875683463</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 34 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875683464</u>
	MGrid IDT Rec W/ LRmp .38AuLF 34Ckt	<u>875683483</u>
	MGrid IDT Rec W/ LRmp .76AuLF 34Ckt	<u>875683484</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 34 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875683493</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 34 Circuits, 0.76µm Gold (Au) Selective Plating, with Center	<u>875683494</u>

	Polarization Key and Locking Friction Ramp	
	MGrid IDT Rec / PolKey .38AuLF 36Ckt	<u>875683643</u>
	MGrid IDT Rec / PolKey .76AuLF 36Ckt	<u>875683644</u>
	MGrid IDT Rec O/ PolKeyLRmp .38AuLF 36Ckt	<u>875683663</u>
	MGrid IDT Rec O/ PolKeyLRmp .76AuLF 36Ckt	<u>875683664</u>
	MGrid IDT Rec W/ PolKeyLRmp .76AuLF 36Ckt	<u>875683694</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 40 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875684043</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 40 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875684044</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 40 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875684063</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 40 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875684064</u>
	MGrid IDT Rec W/ LRmp .38AuLF 40Ckt	<u>875684083</u>
	MGrid IDT Rec W/ LRmp .76AuLF 40Ckt	<u>875684084</u>

	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 40 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875684093</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 40 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875684094</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 44 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875684443</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 44 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875684444</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 44 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875684463</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 44 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875684464</u>
	MGrid IDT Rec W/ LRmp .38AuLF 44Ckt	<u>875684483</u>

	MGrid IDT Rec W/ LRmp .76AuLF 44Ckt	<u>875684484</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 44 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875684493</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 44 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875684494</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 50 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875685043</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 50 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875685044</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 50 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875685063</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 50 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875685064</u>

MGrid IDT Rec W/ LRmp .38AuLF 50Ckt	<u>875685083</u>
MGrid IDT Rec W/ LRmp .76AuLF 50Ckt	<u>875685084</u>
Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 50 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875685093</u>
Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 50 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875685094</u>

This document was generated on 10/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62100-2200](#)