

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0367831204](#)
Status: **Active**
Overview: [MX120G Sealed Connectors](#)
Description: MX120G Sealed Header Connector Assembly, 12 Circuit, Color Mark Identification Green

Documents:
[3D Model](#) [Product Specification PS-36783-001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Application Specification AS-36783-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family PCB Headers
Series [36783](#)
Application Wire-to-Board
Overview [MX120G Sealed Connectors](#)
Product Name MX120G
UPC 884982894136

Physical

(p)ower-(s)ignal Configuration 12p - 0s
Breakaway No
Circuits (Loaded) 12
Circuits (maximum) 12
Color - Resin Black
Durability (mating cycles max) 10
First Mate / Last Break No
Flammability 94HB
Glow-Wire Capable No
Guide to Mating Part No
Lock to Mating Part Yes
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 8.749/g
Number of Rows 2
Orientation Right Angle
PC Tail Length 3.20mm
PCB Thickness - Recommended 1.60mm
Packaging Type Carton
Pitch - Mating Interface 3.20mm
Pitch - Termination Interface 3.50mm
Polarized to Mating Part Yes
Polarized to PCB Yes
Robotic Placement None
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40° to +105°C
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 10.5A
Voltage - Maximum 28V DC



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series

[36783](#) Series

Mates With

[367921201](#) 3.20mm MX120G Pitch Sealed
Female Connector Assembly

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Process Temperature max. C	245

Material Info

Reference - Drawing Numbers

Application Specification	AS-36783-001-001
Product Specification	PS-36783-001-001
Sales Drawing	SD-36783-004-001

This document was generated on 10/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[36783-1204](#)