

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0387207526

Status:


Active

Overview:

Beau Barrier Strips

Description:

9.53mm Pitch Beau PCB Terminal Strip, without Mounting Ends, 26 Circuits, with Screw Clamp Washer



Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-38710-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Terminal Blocks
Series	38720
Application	N/A
Component Type	One Piece
Overview	Beau Barrier Strips
Product Name	Fixed Mount Barrier
Type	Barrier Strip
UPC	800756274324
Physical	
Circuits (Loaded)	26
Circuits (maximum)	26
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Number of Rows	1
Orientation	Horizontal
PC Tail Length	4.80mm
PCB Retention	None
PCB Thickness - Recommended	3.18mm
Panel Mount	No
Pitch - Mating Interface	9.53mm
Pitch - Termination Interface	9.53mm
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	No
Shrouded	Dual-Barrier
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +130°C
Wire Size AWG	12, 14, 16, 18, 20, 22
Wire Size mm²	0.50-2.50
Electrical	
Current - Maximum per Contact	25.0A
Voltage - Maximum	300V
Material Info	
Engineering Number	72526-C-50
Reference - Drawing Numbers	
Product Specification	PS-38710-001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per	
-ED/88/2018 (15	
January 2019)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

38720 Series

Mates With

N/A

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[38720-7526](#)