

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018826

Status:

Active

Overview:

Application Tooling

Description:

Impact Backplane Press-In Tool

Documents:

RoHS Certificate of Compliance (PDF)


General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	884982735163
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-622018826, TM-622018799



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Contained Per	
-ED/01/2018 (15	
January 2018)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207123 Series

Use With

Impact 85 Ohm Backplane Assembly, 4-Pair by 16 Column Assemblies 170335 , 170515

Application Tooling Description	FAQ Product #
Impact 85 Ohm Plus 4 Pair Vertical Header, Unguided, Open End Walls, 16 Columns, 192 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free	1703351604
Impact 85 Ohm Plus 4 Pair Vertical Header, Unguided, Open End Walls, 16 Columns, 192 Circuits, Pin Length	1703351605

5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 85 Ohm	<u>1703351607</u>
Plus 4 Pair Vertical Header, Unguided, Open End Walls, 16 Columns, 192 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 85 Ohm	<u>1703351608</u>
Plus 4 Pair Vertical Header, Unguided, Open End Walls, 16 Columns, 192 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 85 Ohm	<u>1703351614</u>
Plus 4 Pair Vertical Header, Unguided, Left End Wall, 16 Columns, 192 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 85 Ohm	<u>1703351625</u>
Plus 4 Pair Vertical Header, Unguided, Dual End Walls, 16 Columns, 192 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 85 Ohm	<u>1703351627</u>
Plus 4 Pair Vertical Header, Unguided, Dual End Walls, 16 Columns, 192 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 85 Ohm	<u>1703353607</u>
Plus 4 Pair Vertical Header, Left Guide, Open End Walls, 16 Columns, 192 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	

Impact 85 Ohm Plus 4 Pair Vertical Header, Left Guide, Open End Walls, 16 Columns, 144 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>1703353608</u>
Impact 85 Ohm Plus 4 Pair Vertical Header, Right Guide, Open End Walls, 16 Columns, 192 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>1703355607</u>
Impact 85 Ohm Plus 4 Pair Vertical Header, Right Guide, Open End Walls, 16 Columns, 192 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>1703355608</u>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8826](#)