

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395140011

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

3.81mm Pitch Eurostyle Horizontal Plug, with Retention Screws, 11 Circuits

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-39500-001-001 (PDF)

Packaging Specification PK-39500-001-001 (PDF)

Packaging Specification PK-39514-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E48521

General

Product Family

Series

Application

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

39514

N/A

Plug

Eurostyle Terminal Blocks

ESE, Eurostyle Pluggable

Euro Block

822350688987

Physical

Circuits (Loaded)

Entry Angle

Lock to Mating Part

Net Weight

Number of Rows

Orientation

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

Wire Size AWG

Wire Size mm²

11

Vertical

Yes

8.330/g

1

Horizontal

No

3.81mm

3.81mm

Yes

No

-40° to +105°C

16, 18, 20, 22, 24

0.20-1.31

Electrical

Current - Maximum per Contact

Voltage - Maximum

8.0A

300V

Material Info

Reference - Drawing Numbers

Packaging Specification


Product Specification

Sales Drawing

PK-39500-001-001, PK-39514-001-001

PS-39500-001-001

SD-39514-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China RoHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

39514 Series

Mates With

Most 3.81mm Pitch Industry Standard PCB Headers, 39515 Vertical PCB Header with Threaded Retention Inserts, 39516 Horizontal PCB Header with Threaded Retention Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39514-0011](#)