

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018833

Status:

Active

Overview:

Application Tooling

Description:

Impact Backplane Module Installation Press-In Tool


Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	887191002989
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-622018833-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207123 Series

Use With

Impact Backplane Signal Module Assembly, 4-Pair by 12 Column 85 Ohm Assemblies

170335 , 170515

Application Tooling Description	FAQ Product #
Impact 85 Ohm Plus 4 Pair Vertical Header, Unguided, Open End Walls, 12 Columns, 144 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	1703351207
Impact 85 Ohm Plus 4 Pair Vertical Header, Unguided, Open End Walls, 12 Columns, 144	1703351208

Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 85 Ohm	<u>1703351217</u>
Plus 4 Pair Vertical Header, Unguided, Left End Wall, 12 Columns, 144 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 85 Ohm	<u>1703351227</u>
Plus 4 Pair Vertical Header, Unguided, Dual End Walls, 12 Columns, 144 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 85 Ohm	<u>1703353207</u>
Plus 4 Pair Vertical Header, Left Guide, Open End Walls, 12 Columns, 144 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 85 Ohm	<u>1703355207</u>
Plus 4 Pair Vertical Header, Right Guide, Open End Walls, 12 Columns, 144 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 4x12 85 Ohm GL Endwall BP 4.9 .39	<u>1703357207</u>
Impact 85 Ohm	<u>1703359207</u>
Plus 4 Pair Vertical Header, Right Guide, Left End Wall, 12 Columns, 144 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8833](#)