

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622030485

Status:

Active

Overview:

Application Tooling

Description:

Impact Backplane Press-In Tool

Documents:

RoHS Certificate of Compliance (PDF)


General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	884982949416
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-622030485-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207123 Series

Use With

76285 Impact Orthogonal Backplane Signal Module Assembly, (6-Pair by 12 Column Assemblies)

Application Tooling Description	FAQ Product #
Impact 100 Ohm 6 Pair Vertical Orthogonal Header Unguided, Open Endwall, 12 Columns, 216 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free	762851205
Impact 100 Ohm 6 Pair Vertical Orthogonal Header, Unguided, Open Endwall, 12 Columns, 216	762851208

Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead Free Impact 100 Ohm	<u>762851224</u>
6 Pair Vertical Orthogonal Header Unguided, Dual Endwall, 12 Columns, 216	
Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>762851225</u>
6 Pair Vertical Orthogonal Header Unguided, Dual Endwall, 12 Columns, 216	
Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>762851227</u>
6 Pair Vertical Orthogonal Header Unguided, Dual Endwall, 12 Columns, 216	
Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>762851228</u>
6 Pair Vertical Orthogonal Header Unguided, Dual Endwall, 12 Columns, 216	
Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>762853208</u>
6 Pair Vertical Orthogonal Header, Left Guided, Open Endwall, 12 Columns, 216	
Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead Free Impact 100 Ohm	<u>762855208</u>
6 Pair Vertical Orthogonal Header, Right Guided, Open Endwall,	

12 Columns, 216 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead Free Impact 100 Ohm	<u>762857204</u>
6 Pair Vertical Orthogonal Header Left Guided, Right Endwall, 12 Columns, 216 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>762857205</u>
6 Pair Vertical Orthogonal Header Left Guided, Right Endwall, 12 Columns, 216 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>762857207</u>
6 Pair Vertical Orthogonal Header Left Guided, Right Endwall, 12 Columns, 216 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>762857208</u>
6 Pair Vertical Orthogonal Header Left Guided, Right Endwall, 12 Columns, 216 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>762859207</u>
6 Pair Vertical Orthogonal Header Right Guided, Left Endwall, 12 Columns, 216 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>762859208</u>

Left Endwall, 12
Columns, 216
Circuits, Pin Length
5.50mm, Plated
Through Hole
Dimension 0.39mm,
Lead-Free

This document was generated on 07/28/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62203-0485](#)