

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0638019200
Status: Active
Overview: Application Tooling
Description: Bench Top Pneumatic Wire Stripper for 12-26 AWG

Documents:
[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Application Tooling
Series 207122
Comments See Tooling Specification (PDF) Above
Function Wire Stripping
Geographic Area Global
Level of Automation Semi-Automatic
More Detailed Tech Information applicationtooling@molex.com
Overview Application Tooling
Product Name N/A
Tool Type Pneumatic Wire Stripper
UPC 884982191051
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info
Engineering Number WS-1000

Reference - Drawing Numbers
Application Tooling Documents TM-638019200-001, TM-638019200CN-001, TM-638019200DE-001, TM-638019200FR-001, TM-638019200IT-001, TM-638019200JP-001, TM-638019200KR-001, TM-638019200MY-001, TM-638019200PL-001, TM-638019200RU-001, TM-638019200SK-001, TM-638019200SP-001, TM-638019200TH-001, TM-638019200TW-001, TM-638019200VN-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/30/2017 (7 July 2017)	
Halogen-Free Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
207122 Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63801-9200](#)