

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0639043400](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Fine Adjust Applicator for Ultra-Fit Tangless Crimp Terminals, 20-22 AWG (UL 1061) Wires

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Application Tooling
Series	207127
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	FineAdjust
Tool Type	Applicator
UPC	193264137152
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers
Application Tooling Documents 639043400-000



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[207127](#) Series

Application Tooling Description	FAQ Product #
Ultra-Fit Tangless Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 20-22 AWG	1722536111
Ultra-Fit Tangless Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 20-22 AWG	1722536112
Ultra-Fit Tangless Crimp Terminal, Female, Tin (Sn) Plating, 20-22 AWG	1722537123

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63904-3400](#)