

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0424108314

Status:

Active

Overview:

Magnetic and Modular Jacks/Plugs

Description:

Modular Jack, Vertical, 8/8

Documents:

3D Model (PDF)

Packaging Specification PK-42410-492-001 (PDF)

Drawing (PDF)

Test Summary TS-42878-001-001 (PDF)

3D Model

RoHS Certificate of Compliance (PDF)

Product Specification PS-42410-001 (PDF)

Agency Certification		
CSA		LR19980
UL		E107635
General		
Product Family		Modular Jacks/Plugs
Series		42410
Comments		Flush Mount Flangeless 2 PCB Thick
Component Type		PCB Jack
Magnetic		No
Overview		Magnetic and Modular Jacks/Plugs
Performance Category		3
Power over Ethernet (PoE)		N/A
Product Name		Modular Jack 8/8, RJ45
UPC		800754381147

Physical		
Color - Resin		Black
Durability (mating cycles max)		500
Flammability		94V-0
Inverted / Top Latch		N/A
Jack Height		16.38mm
Lightpipes/LEDs		None
Material - Metal		Phosphor Bronze
Material - Plating Mating		Gold
Material - Plating Termination		Tin
Material - Resin		Polyester
Net Weight		2.694/g
Orientation		Vertical (Top Entry)
PCB Retention		Yes
PCB Thickness - Recommended		1.60mm
Packaging Type		Tray
Pitch - Mating Interface		1.02mm
Pitch - Termination Interface		1.27mm
Plating min - Mating		1.270µm
Plating min - Termination		2.540µm
Port Configuration		1x1
Positions / Loaded Contacts		8/8
Surface Mount Compatible (SMC)		No
Temperature Range - Operating		-40° to +80°C
Termination Interface: Style		Through Hole
Wire/Cable Type		N/A

Electrical		
Current - Maximum per Contact		1.5A
Shielded		No



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

42410 Series

Mates With

FCC 68 Plugs

Voltage - Maximum	125V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-42410-492-001
Product Specification	PS-42410-001
Sales Drawing	SDA-42410-XXXX-001
Test Summary	TS-42878-001-001

This document was generated on 09/20/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

42410-8314