

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0428910140](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: KK 396 Solid Vertical Header, Friction Lock, with Snap-in Plastic Peg PCB Lock, 5 Circuits, 0.76µm Gold (Au) Selective Plating

Documents:

[3D Model](#) [Packaging Specification PK-42491-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-08-50-001 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family PCB Headers
Series [42891](#)
Application Power, Wire-to-Board
CURRENT-MAX-NUMERIC 7.0
Overview [KK® Interconnect System - Molex](#)
PITCH-MATING-NUMERIC 3.96
Product Name KK 396
UPC 756054535707

Physical

Breakaway No
Circuits (Loaded) 5
Circuits (maximum) 5
Durability (mating cycles max) 100
Flammability 94V-0
Glow-Wire Capable No
Lock to Mating Part Yes
Material - Metal Brass
Material - Plating Mating Gold
Material - Plating Termination Tin
Net Weight 1.908/g
Number of Rows 1
Orientation Vertical
PC Tail Length 3.56mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Bag
Pitch - Mating Interface 3.96mm
Plating min - Mating 0.762µm
Plating min - Termination 2.540µm
Polarized to Mating Part No
Polarized to PCB Yes
Shrouded No
Stackable Yes
Temperature Range - Operating See Product Specification
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 7.0A
Voltage - Maximum 250V

Solder Process Data



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[42891](#) Series

Mates With

[2139](#) KK Crimp Housing, [41695](#) KK Crimp Housing, [6442](#) KK Crimp Housing, [2145](#) PCB Connector, [41815](#) PCB Connector, [3069](#) KK Crimp Housing

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-42491-001-001
Product Specification	PS-08-50-001
Sales Drawing	SD-42891-001-002

This document was generated on 06/07/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[42891-0140](#)