

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0431601103](#)
Status: **Active**
Overview: [Sabre Power Connector](#)
Description: Sabre Right-Angle Header, 3 Circuits, Glow-Wire Capable, PCB Thickness 1.60mm, without Board Lock

Documents:

Drawing (PDF)	Test Summary 444410000-TS-000 (PDF)
3D Model	Symbol Footprint Data SYM-43160-1103 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-44441-9999-001 (PDF)	Product Literature (PDF)
Packaging Specification PK-43160-0010-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179


General

Product Family	PCB Headers
Series	43160
Application	Power, Wire-to-Board
Comments	<p>*****Fully Polarized, high power wire to board and wire to wire connector system<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies: a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.*****</p>

Overview	Sabre Power Connector
Product Name	Sabre
UPC	800754377812

Physical

Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)4578-DC (25 June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[43160 Series](#)

Mates With

[444412003 Sabre Receptacle Housing](#)

Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	4.245/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.81mm
PCB Locator	Yes
PCB Retention	N/A
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	7.50mm
Pitch - Termination Interface	7.50mm
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +75°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	18.0A
Voltage - Maximum	600V

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-free Process Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-43160-0010-001
Product Specification	PS-44441-9999-001
Sales Drawing	431600001-SD-000
Symbol/Footprint Data	SYM-43160-1103
Test Summary	444410000-TS-000

This document was generated on 09/29/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[43160-1103](#)