

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0432550145

Status:

Active

Overview:

MLX Power Connectors

Description:

6.35mm Pitch MLX Power Connector Header, 2.13mm Contact Diameter, Vertical, with Plastic Polarizing Peg, 9 Circuits, PA Polyamide Nylon 6/6 94V-2, Tin (Sn) Plating, Natural (Nylon Off Natural), Lead-Free

Documents:

3D Model (PDF)

3D Model

Drawing (PDF)

Product Specification PSX-42002-0001-001 (PDF)

Packaging Specification PK-43255-001-001 (PDF)

Packaging Specification PK-43255-003-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	43255
Application	Board-to-Board, Power, Wire-to-Board
Comments	High Vibration Application
Overview	MLX Power Connectors
Product Name	MLX
UPC	800753948938

Physical

Breakaway	No
Circuits (Loaded)	9
Circuits (maximum)	9
Color - Resin	Natural
Durability (mating cycles max)	50
First Mate / Last Break	No
Flammability	94V-2
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Mated Height	30.35mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	5.017/g
Number of Rows	3
Orientation	Vertical
PC Tail Length	4.30mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	6.35mm
Pitch - Termination Interface	6.35mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

43255 Series

Mates With

42021 MLX Power Crimp Housing Plug,
42023 MLX Crimp Terminal, 42024 MLX
Crimp Terminal

Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	20.0A, 9.0A
Voltage - Maximum	600V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	WAVE
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-43255-001-001, PK-43255-003-001
Product Specification	PSX-42002-0001-001
Sales Drawing	SDA-43255-00XX-001

This document was generated on 12/21/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[43255-0145](#)