

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0737801125

Status:


Active

Overview:

HDM Backplane Connector System

Description:

HDM Board-to-Board Daughtercard Receptacle, Vertical, Signal Module, 144 Circuits, Mounted Height 15.00mm, Pin Length 2.00mm, Solder Tail



Series image - Reference only

|                                |                                                              |
|--------------------------------|--------------------------------------------------------------|
| Documents:                     |                                                              |
| <a href="#">3D Model</a>       | <a href="#">Product Specification PS-73780-999-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>  | <a href="#">RoHS Certificate of Compliance (PDF)</a>         |
| <a href="#">3D Model (PDF)</a> |                                                              |

|                                |                                |
|--------------------------------|--------------------------------|
| Agency Certification           |                                |
| UL                             | E29179                         |
| General                        |                                |
| Product Family                 | Backplane Connectors           |
| Series                         | 73780                          |
| Application                    | Daughtercard, Mezzanine        |
| Comments                       | Solder Tail                    |
| Component Type                 | PCB Receptacle                 |
| Overview                       | HDM Backplane Connector System |
| Product Name                   | HDM                            |
| UPC                            | 800754870481                   |
| Physical                       |                                |
| Circuits (Loaded)              | 144                            |
| Circuits (maximum)             | 144                            |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 250                            |
| First Mate / Last Break        | No                             |
| Flammability                   | 94V-0                          |
| Guide to Mating Part           | No                             |
| Keying to Mating Part          | None                           |
| Material - Metal               | Copper-Nickel-Tin              |
| Material - Plating Mating      | Gold                           |
| Material - Plating Termination | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 20.030/g                       |
| Number of Columns              | 24                             |
| Number of Pairs                | Open Pin Field                 |
| Number of Rows                 | 6                              |
| Orientation                    | Vertical                       |
| PC Tail Length                 | 2.00mm                         |
| PCB Locator                    | No                             |
| PCB Retention                  | None                           |
| PCB Thickness - Recommended    | 1.60mm                         |
| Packaging Type                 | Tube                           |
| Pitch - Mating Interface       | 2.00mm                         |
| Pitch - Termination Interface  | 2.00mm                         |
| Plating min - Mating           | 0.762µm                        |
| Plating min - Termination      | 2.540µm                        |
| Polarized to PCB               | No                             |
| Stackable                      | Yes                            |
| Surface Mount Compatible (SMC) | Yes                            |
| Temperature Range - Operating  | -55° to +105°C                 |
| Termination Interface: Style   | Through Hole                   |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2020)9139-DC (19 Jan 2021)              |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Low-Halogen                                                   |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

73780 Series

Mates With

HDM Board-to-Board Backplane Header

[73642](#) , [73643](#) , [73644](#) , [73942](#) , [73943](#) , [73944](#) , [74349](#) , [74428](#). HDM Board-to-Board Stacking Header, [73769](#) , [73770](#) , [73782](#) , [73783](#) , [73771](#)

**Electrical**

|                               |             |
|-------------------------------|-------------|
| Current - Maximum per Contact | 15.0A, 1.0A |
| Data Rate                     | 1.0 Gbps    |
| Real Signals (per 25mm)       | 75          |
| Shielded                      | No          |
| Voltage - Maximum             | 250V AC     |

**Solder Process Data**

|                                                |      |
|------------------------------------------------|------|
| Duration at Max. Process Temperature (seconds) | 005  |
| Lead-freeProcess Capability                    | WAVE |
| Max. Cycles at Max. Process Temperature        | 001  |
| Process Temperature max. C                     | 260  |

**Material Info**

**Reference - Drawing Numbers**

|                       |                  |
|-----------------------|------------------|
| Product Specification | PS-73780-999-001 |
| Sales Drawing         | SD-73780-004     |

This document was generated on 03/24/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[73780-1125](#)