

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0440500002

Status:

Active

Overview:

Magnetic and Modular Jacks/Plugs

Description:

Modular Jack, Right-Angle, Low Profile, 8/8

Documents:

3D Model

Packaging Specification PK-44050-004-001 (PDF)

Drawing (PDF)

Test Summary TS-44050-001-001 (PDF)

3D Model (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E107635

General

Product Family

Modular Jacks/Plugs

Series

44050

Component Type

PCB Jack

Magnetic

No

Overview

Magnetic and Modular Jacks/Plugs

Performance Category

5, 5e

Power over Ethernet (PoE)

N/A

Product Name

Modular Jack 8/8, RJ45

UPC

800753940161

Physical

Boot Color

N/A

Color - Resin

Black

Durability (mating cycles max)

500

Flammability

94V-0

Inverted / Top Latch

No

Jack Height

13.06mm

Lightpipes/LEDs

None

Material - Metal

Brass, Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

5.267/g

Orientation

Right Angle (Side Entry)

PCB Locator

Yes

PCB Retention

Yes

PCB Thickness - Recommended

1.57mm

Packaging Type

Tray

Pitch - Mating Interface

1.02mm

Pitch - Termination Interface

1.27mm

Plating min - Mating

1.270µm

Plating min - Termination

2.540µm

Port Configuration

1x1

Positions / Loaded Contacts

8/8

Surface Mount Compatible (SMC)

Yes

Temperature Range - Operating

-40° to +85°C

Termination Interface: Style

Through Hole

Waterproof / Dustproof

No


Wire/Cable Type

N/A

Electrical

Current - Maximum per Contact

1.5A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

44050 Series

Mates With

FCC 68 Plugs

Grounding to Panel	Location E, With All Panel Grounding Tab
Shielded	Yes
Voltage - Maximum	150V AC (RMS)

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-44050-004-001
Sales Drawing	SD-44050-002-001
Test Summary	TS-44050-001-001

This document was generated on 08/25/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[44050-0002](#)