


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0451110405
Status: Active
Overview: Micro-Lock Plus Wire-to-Board Connector System
Description: Micro-Lock PLUS-to-Micro-Lock PLUS Off-the-Shelf (OTS) Cable Assembly, 1.25mm Pitch, Single Row, 450.00mm Length, 4 Circuits, Black



Documents:
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	45111
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Lock PLUS Both Ends
Overview	Micro-Lock Plus Wire-to-Board Connector System
Product Literature Order No	987651-6143
Product Name	Micro-Lock PLUS OTS
UPC	191128368520
Physical	
Cable Length	450.00mm
Circuits (Loaded)	4
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	4.436/g
Packaging Type	Bag
Pitch - Mating Interface	1.25mm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.98mm
Wire Size AWG	26
Wire/Cable Type	UL 1061
Electrical	
Voltage - Maximum	50V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	451110400-000

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per -ED/01/2018 (15 January 2018) Halogen-Free Status Not Low-Halogen Need more information on product environmental compliance? Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	China RoHS China ROHS ELV RoHS Phthalates
	Green Image Not Relevant Not Contained

Search Parts in this Series
[45111](#) Series

Mates With
Single Row Vertical Header [505568](#) ,

Single Row Right Angle Header [505567](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[45111-0400](#) [45111-0401](#) [45111-0405](#) [45111-0402](#) [45111-0403](#) [45111-0406](#)