

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0458450001](#)
Status: **Active**
Overview: [Edge Card Connectors](#)
Description: 2.50mm Pitch EXTreme PowerEdge Signal Connector, Double Sided, 2 Segments, 8 Signal Contacts per Segment, Press-Fit

Documents:

3D Model	Packaging Specification PK-45714-001-001 (PDF)
Drawing (PDF)	Test Summary TS-45844-001-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-45719-001-001 (PDF)	

Agency Certification

CSA	LR19980
TUV	30482572

General

Product Family	Edge Card Connectors
Series	45845
Component Type	Edgecard to PCB
Data Rate	Unrated
Edge Card Thickness	1.57mm
High Power Bay (30.0A or more)	No
Orientation	Vertical
Overview	Edge Card Connectors
Product Name	EXTreme PowerEdge
Standard Based	General
UPC	822348846528


Physical

(p)ower-(s)ignal Configuration	16s - 0p
Circuit Size Range	1-64 Circuits
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
Durability (mating cycles max)	250
Entry Angle	Vertical (Top Entry)
Flammability	94V-0
Keying to Mating Part	N/A
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.382/g
PC Tail Length	4.50mm
PCB Thickness - Recommended	2.40mm
Packaging Type	Tray
Pitch - Mating Interface	2.50mm
Plating min - Mating	0.762µm
Plating min - Termination	3.810µm
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Solder Process Data



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[45845 Series](#)

Mates With

1.58mm Double Sided Card Edge

Lead-free	Process Capability	N/A
Material Info		
Reference - Drawing Numbers		
Packaging Specification		PK-45714-001-001
Product Specification		PS-45719-001-001
Sales Drawing		SD-45845-001-001
Test Summary		TS-45844-001-001

This document was generated on 09/20/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[45845-0001](#)