

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0459846911](#)
Status: **Active**
Overview: [EXTreme LPHPower Connectors](#)
Description: EXTreme LPHPower Receptacle Header, Right-Angle, 6 Power Contacts, Select Gold (Au) Plating, for 3.18mm Thick PC Board

Documents:

3D Model	Packaging Specification PK-45984-001-001 (PDF)
3D Model (PDF)	Symbol Footprint Data SYM-45984-6911-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-45984-001-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Receptacles
Series	45984
Application	Board-to-Board, Power
Comments	6 Power Blades
Overview	EXTreme LPHPower Connectors
Product Name	EXTreme LPHPower
UPC	800756650883

Physical

(p)ower-(s)ignal Configuration	6p - 0s
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	250
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	7.602/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	4.50mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	3.18mm
Packaging Type	Tray
Pitch - Mating Interface	12.00mm
Pitch - Termination Interface	2.00mm, 2.50mm
Plating min - Mating	0.762µm
Plating min - Termination	3.810µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[45984](#) Series

Mates With

[45985](#) EXTreme LPHPower Headers

Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	27.0A
Grounding to PCB	No
Voltage - Maximum	250V AC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	015
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	230
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-45984-001-001
Product Specification	PS-45984-001-001
Sales Drawing	SD-45984-102-001
Symbol/Footprint Data	SYM-45984-6911-001

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[45984-6911](#)