

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0740588512

Status:


Active

Overview:

VHDM Backplane Connector Systems

Description:

VHDM Single-Ended Board-to-Board Backplane Header, 2.00mm Pitch, Vertical, 6 Rows, Guide Pin Signal Module, Pin End Version, 150 Circuits, 25 Columns, Pin Length 6.25mm, Key Orientation A



Documents:

Drawing (PDF)

Product Specification PS-74031-999-001 (PDF)

Packaging Specification PK-74058-003 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Backplane Connectors
Series	74058
Application	Backplane
Application Tooling Documents	TM-622010999
Comments	Keying Position A
Component Type	PCB Header
Overview	VHDM Backplane Connector Systems
Product Name	VHDM
UPC	822350225250
Physical	
Circuits (Loaded)	150
Circuits (maximum)	150
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Net Weight	14.566/g
Number of Columns	25
Number of Pairs	Open Pin Field
Number of Rows	6
Orientation	Vertical
PC Tail Length	2.50mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.80mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	105°C
Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	2.0A
Data Rate	3.125 Gbps
Shield Type	Ground Plane Shield
Shielded	Yes
Voltage - Maximum	120V AC (RMS)/DC

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

ECHA_01_2020 (16

January 2020

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

74058 Series

Mates With

74030 VHDM Board-to-Board Daughtercard

Receptacle

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Signal Pin Inserter	622015700
Repair Tool	
6-Row Pin and	622015800
Shield Repair Tool	
6-Row Shield	622016000
Extraction Tool	
Insertion Module	622020204
for Advanced Mate	
Signal Header, 6-	

Solder Process Data		N/A	Row by 25-Wide, 50.00mm Insertion Module <u>622020208</u> for Standard Shield Signal Header, 6- Row by 25-Wide, 50.00mm
Lead-freeProcess Capability			
Material Info			
Reference - Drawing Numbers			
Packaging Specification		PK-74058-003	
Product Specification		PS-74031-999-001	
Sales Drawing		SD-74058-002	

This document was generated on 04/14/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

74058-8512