

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0740602504

Status:

Active

Overview:

VHDM Backplane Connector Systems

Description:

VHDM Single-Ended Board-to-Board Backplane Header, 2.00mm Pitch, Vertical, 8 Rows, Open Signal Module, 200 Circuits, 25 Columns, Pin Length 5.15mm

Documents:

3D Model (PDF)

Drawing (PDF)

3D Model

Product Specification PS-74031-999-001 (PDF)

Packaging Specification PK-74060-003-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Application Tooling Documents

Comments

Component Type

Overview

Product Name

UPC

Backplane Connectors

74060

Backplane

TM-622010999-001

Open Header

PCB Header

VHDM Backplane Connector Systems

VHDM

800753260047

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Guide to Mating Part

Keying to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Columns

Number of Pairs

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to PCB

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

200

200

Black

200

No

94V-0

No

None

Beryllium Copper, High Performance Alloy (HPA)

Gold

Matte Tin

High Temperature Thermoplastic

13.630/g

25

Open Pin Field

8

Vertical

2.50mm

No

None

1.80mm

Tube

2.00mm

1.00mm

0.762µm

0.762µm

Yes

Yes

-55° to +105°C

Through Hole - Compliant Pin



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

74060 Series

Mates With

74040 VHDM Board-to-Board Daughtercard

Receptacle

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Signal Pin Inserter	622015700
Repair Tool	
8-Row Pin and	622015900
Shield Repair Tool	
8-Row Shield	622016100
Extraction Tool	

Electrical

Current - Maximum per Contact	3.0A
Data Rate	3.125 Gbps
Shield Type	Ground Plane Shield
Shielded	Yes
Voltage - Maximum	120V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-74060-003-001
Product Specification	PS-74031-999-001
Sales Drawing	SD-74060-002-001

This document was generated on 09/21/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74060-2504](#)