

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0740622514

Status:


Active

Overview:

VHDM® Backplane Connector Systems

Description:

2.00mm Pitch VHDM® Single-Ended Board-to-Board Backplane Header, Vertical, 8-Row, Guide Pin Signal Module, Shield End Version, 200 Circuits, Pin Length 5.15mm, Keying Pin Orientation A. Series:74075 Enables designers to create custom loaded connectors utilizing standard pin lengths 4.25, 4.75, 5.15 and 6.25mm25, 4.75, 5.15 and 6.25mm



Series image - Reference only

Documents:

Drawing (PDF)

Product Specification PS-74031-999 (PDF)

Packaging Specification PK-74061-003 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
General	
Product Family	Backplane Connectors
Series	74062
Application	Backplane
Application Tooling Documents	TM-622010999
Comments	Keying Position A
Component Type	PCB Header
Overview	VHDM® Backplane Connector Systems
Product Name	VHDM®
UPC	800753259287
Physical	
Circuits (Loaded)	200
Circuits (maximum)	200
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Material - Metal	Beryllium Copper, High Performance Alloy (HPA), Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Material - Resin	High Temperature Thermoplastic
Net Weight	17.210/g
Number of Columns	25
Number of Pairs	Open Pin Field
Number of Rows	8
Orientation	Vertical
PC Tail Length	2.50mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.80mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	Yes

EU ELV

Not Relevant

EU RoHS

China RoHS

Not Compliant

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

Search Parts in this Series

74062 Series

Mates With

74040 VHDM® Board-to-Board Daughtercard Receptacle

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Module for Standard Shield Signal Header, 8-Row by 25-Wide, 50.00mm	0622020210

Temperature Range - Operating	-55°C to +105°C	Signal Pin Inserter	0622015700
Termination Interface: Style	Through Hole - Compliant Pin	Repair Tool	
Electrical		8-Row Pin and	0622015900
Current - Maximum per Contact	3.0A	Shield Repair Tool	
Data Rate	3.125 Gbps	Insertion Module	0622020206
Shield Type	Ground Plane Shield	for Advanced Mate	
Shielded	Yes	Signal Header, 6-	
Voltage - Maximum	120V AC (RMS)/DC	Row by 25-Wide,	
		50.00mm	
Solder Process Data		8-Row Shield	0622016100
Lead-freeProcess Capability	N/A	Extraction Tool	
Material Info			
Reference - Drawing Numbers			
Packaging Specification	PK-74061-003		
Product Specification	PS-74031-999		
Sales Drawing	SD-74062-002		

Note: HDM, HDM+, VHDM, VHDM-HSD and GbX are trademarks or registered trademarks of Amphenol TCS.

This document was generated on 09/29/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74062-2514](#)