

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0741620430

Status:

Active

Overview:

C-Grid Connector Products

Description:

2.54mm Pitch C-Grid Receptacle, Right-Angle, Through Hole, Dual Row, Shrouded, Version A, High-Temperature, 30 Circuits, 0.80µm Gold (Au)

Documents:	
3D Model	Product Specification PS-74162-001-001 (PDF)
3D Model (PDF)	Application Specification 713080001-AS-000 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Receptacles
Series	74162
Application	Board-to-Board, Signal
Overview	C-Grid Connector Products
Product Name	C-Grid
UPC	883906879617
Physical	
Circuits (Loaded)	30
Circuits (maximum)	30
Color - Resin	Black
Durability (mating cycles max)	50
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Performance Thermoplastic
Net Weight	6.174/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	3.18mm
Packaging Type	Tube
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.762µm
Polarized to Mating Part	No
Polarized to PCB	No
Robotic Placement	None
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	2.5A
Grounding to PCB	No



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ECHA_01_2020 (16 January 2020)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[74162](#) Series

Mates With

C-Grid Vertical Receptacle [71395](#) , [71850](#)

Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Application Specification	713080001-AS-000
Product Specification	PS-74162-001-001
Sales Drawing	SD-74162-001

This document was generated on 05/01/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

74162-0430