

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0461120201

Status:

Active

Overview:

EXTreme LPHPower Connectors

Description:

12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 2 Power Contact, Select Gold (Au) Plating, without BMI Guides

Documents:	
3D Model	Application Specification AS-46114-001-001 (PDF)
3D Model (PDF)	Packaging Specification PK-46114-003-001 (PDF)
Drawing (PDF)	Symbol Footprint Data SYM-46112-0201-001 (PDF)
Product Specification PS-46114-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Receptacles
Series	46112
Application	Board-to-Board, Power
Overview	EXTreme LPHPower Connectors
Product Name	EXTreme LPHPower
UPC	800756885759
Physical	
(p)ower-(s)ignal Configuration	2p - 0s
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Durability (mating cycles max)	250
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.840/g
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Tube
Pitch - Mating Interface	12.00mm
Pitch - Termination Interface	12.00mm
Plating min - Mating	0.762µm
Plating min - Termination	1.270µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

46112 Series

Mates With

45985 EXTreme LPHPower Header

Current - Maximum per Contact	Contact Molex
Grounding to PCB	No
Voltage - Maximum	250V AC (RMS)/DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-46114-001-001
Packaging Specification	PK-46114-003-001
Product Specification	PS-46114-001-001
Sales Drawing	SD-46112-200-001
Symbol/Footprint Data	SYM-46112-0201-001

This document was generated on 08/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[46112-0201](#)