

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0461141020

Status:

Active

Overview:

EXTreme LPHPower Connectors

Description:

1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Vertical, 10 Power Contacts, 20 Signal Contacts, Select Gold (Au) Plating, with BMI Guides

Documents:

3D Model

Application Specification AS-46114-001-001 (PDF)

3D Model (PDF)

Packaging Specification PK-46114-003-001 (PDF)

Drawing (PDF)

Symbol Footprint Data SYM-46114-1020-001 (PDF)

Product Specification PS-46114-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19880

UL

E29179

Application tooling part link

Application Tooling Part Link

62100-6300

Application Tooling Part Link

62201-8671

General

Product Family

PCB Receptacles

Series

46114

Application

Board-to-Board, Power

Comments

Press Fit Pin

Overview

EXTreme LPHPower Connectors

Product Name

EXTreme LPHPower

UPC

800756886299

Physical

(p)ower-(s)ignal Configuration

10p - 20s

Circuits (Loaded)

30

Circuits (maximum)

30

Color - Resin

Black

Durability (mating cycles max)

250

Flammability

94V-0

Glow-Wire Capable

No

Guide to Mating Part

Yes

Keying to Mating Part

None

Lock to Mating Part

None

Material - Metal

High Performance Alloy (HPA)

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

12.440/g

Number of Rows

2

Orientation

Vertical

PCB Locator

No

PCB Retention

None

Packaging Type

Tube

Pitch - Mating Interface

1.27mm, 12.00mm

Pitch - Termination Interface

1.27mm, 2.50mm

Plating min - Mating

0.762µm

Plating min - Termination

2.540µm

Polarized to Mating Part


Yes

Polarized to PCB

Yes

Stackable

No



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

46114 Series

Mates With

45985 EXTreme LPHPower Header

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
LPH Vertical Receptacle Power Terminal Removal Tool	621006300
Vertical Receptacle Press-In Tool	622018671

Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact	30.0A
Grounding to PCB	No
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-46114-001-001
Packaging Specification	PK-46114-003-001
Product Specification	PS-46114-001-001
Sales Drawing	SD-46114-100-001
Symbol/Footprint Data	SYM-46114-1020-001

This document was generated on 01/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[46114-1020](#)