

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0751992513

Status:


Active

Overview:

VHDM L-Series Backplane Connectors

Description:

VHDM L-Series Single-Ended Backplane Header, 2.00mm Pitch, Guide Pin Signal Module, Shield End Version, 8 Rows, 200 Circuits, 25 Columns, Pin Length 4.25m, Key Orientation A, Lead-Free



Documents:

Drawing (PDF)

Product Specification PS-74031-999-001 (PDF)

Packaging Specification PK-74061-003 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Backplane Connectors
Series	75199
Application	Backplane
Application Tooling Documents	TM-622010999
Comments	Keying Position A, Keying Position A
Component Type	PCB Header
Overview	VHDM L-Series Backplane Connectors
Product Name	VHDM L-Series
UPC	822350644396
Physical	
Circuits (Loaded)	200
Circuits (maximum)	200
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA), Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	11.410/g
Number of Columns	25
Number of Pairs	Open Pin Field
Number of Rows	8
Orientation	Vertical
PC Tail Length	2.50mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.80mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	3.0A
Data Rate	622.0 Mbps
Voltage - Maximum	120V AC (RMS)/DC

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

ED/71/2019 (16 July

2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

75199 Series

Mates With

75191 VHDM L-Series Board-to-Board Daughtercard

Use With

Daughtercard Modules

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Signal Pin Inserter

Product #

622015700

Repair Tool

Solder Process Data

Lead-free	Process Capability	N/A
-----------	--------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-74061-003
Product Specification	PS-74031-999-001
Sales Drawing	SD-75199-001

This document was generated on 09/27/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75199-2513](#)