

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0744410010](#)
Status: **Active**
Overview: [XFP Products](#)
Description: 0.80mm Pitch SFP, SFP Plus (SFP+) Host Connector, Z-Axis Pluggable, Right-Angle, Surface Mount, 20 Circuits, 0.76µm Gold (Au)

Documents:

3D Model	Application Specification AS-74441-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-70873-1201 (PDF)
Product Specification PS-74441-001 (PDF)	Test Summary TS-74441-0003 (PDF)
Product Specification TS-74441-002-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification TS-74441-010-001 (PDF)	

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	I/O Connectors
Series	74441
Application	Module-to-Board
Component Type	Receptacle
Electrical Model	Yes
Overview	XFP Products
Product Name	SFP, SFP Plus, SFP+
Type	N/A
UPC	800756382647

Physical

Boot Color	N/A
Circuits (Loaded)	20
Circuits (maximum)	20
Circuits Detail	20
Color - Resin	Black
Durability (mating cycles max)	200
Flammability	94V-0
Gender	Receptacle
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.700/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Panel Mount	No
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Ports	1



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[74441](#) Series

Mates With

SFP Modules

Use With

EMI Shield, [73927](#) SFP Cage, [86025](#) LC Duplex Cable Assembly, Guide Frame, [73939](#) HSSDC2 Cable Assembly

Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Surface Mount
Waterproof / Dustproof	No
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	0.5A
Grounding to Panel	Yes
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	040
Lead-free Process Capability	REFLOW
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info**Reference - Drawing Numbers**

Application Specification	AS-74441-001-001
Electrical Model Document	EE-74441-001
Packaging Specification	PK-70873-1201
Product Specification	PS-74441-001, TS-74441-002-001, TS-74441-010-001
S-Parameter Model	SP-74441-001
Sales Drawing	SD-74441-001-001
Test Summary	TS-74441-0003

This document was generated on 10/26/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74441-0010](#)