

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0621002170

Status:

Active

Overview:

Application Tooling

Description:

Removal Tool for Impact Mezzanine 100 Ohm Vertical Header


Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification Above
Function	Removal
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impact
Tool Type	Press-Fit Extraction Tool
UPC	887191205045
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-621002170-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207123 Series

Use With

76530 Impact Mezzanine 100 Ohm Vertical Header 28, 38, and 40mm and Stack Height

Application Tooling Description	FAQ Product #
Impact 100 Ohm 5 Pair Mezzanine Receptacle, 28mm Stack Height, Unguided, 10 Columns, 150 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free	765301020
Impact 100 Ohm 5 Pair Mezzanine Receptacle, 28mm Stack Height, Unguided, 16 Columns, 240	765301026

	Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>765301030</u> 5 Pair Mezzanine Receptacle, 38mm Stack Height, Unguided, 10 Columns, 150
	Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>765301032</u> 5 Pair Mezzanine Receptacle, 38mm Stack Height, Unguided, 12 Columns, 180
	Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>765301036</u> 5 Pair Mezzanine Receptacle, 38mm Stack Height, Unguided, 16 Columns, 240
	Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>765301037</u> 5 Pair Mezzanine Receptacle, 38mm Stack Height, Unguided, 14 Columns, 210
	Circuits, Plated Through Hole Dimension 0.39mm, Lead Free Impact 100 Ohm <u>765301040</u> 5 Pair Mezzanine Receptacle, 40mm Stack Height, Unguided, 10 Columns, 150
	Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>765301042</u> 5 Pair Mezzanine Receptacle, 40mm Stack Height, Unguided, 12 Columns, 180
	Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free

	Impact 100 Ohm	<u>765301046</u>
	5 Pair Mezzanine	
	Receptacle, 40mm	
	Stack Height,	
	Unguided, 16	
	Columns, 240	
	Circuits, Plated	
	Through Hole	
	Dimension 0.39mm,	
	Lead-Free	
	Impact 100 Ohm	<u>765301047</u>
	5 Pair Mezzanine	
	Receptacle, 40mm	
	Stack Height,	
	Unguided, 14	
	Columns, 210	
	Circuits, Plated	
	Through Hole	
	Dimension 0.39mm,	
	Lead Free	
	Impact 100 Ohm	<u>765303030</u>
	5 Pair Mezzanine	
	Receptacle, 38mm	
	Stack Height, Left	
	Guided, 10 Columns,	
	150 Circuits, Plated	
	Through Hole	
	Dimension 0.39mm,	
	Lead-Free	
	Impact 100 Ohm	<u>765303036</u>
	5 Pair Mezzanine	
	Receptacle, 38mm	
	Stack Height, Left	
	Guided, 16 Columns,	
	240 Circuits, Plated	
	Through Hole	
	Dimension 0.39mm,	
	Lead-Free	
	Impact 100 Ohm	<u>765303040</u>
	5 Pair Mezzanine	
	Receptacle, 40mm	
	Stack Height, Left	
	Guided, 10 Columns,	
	150 Circuits, Plated	
	Through Hole	
	Dimension 0.39mm,	
	Lead-Free	
	Impact 100 Ohm	<u>765303042</u>
	5 Pair Mezzanine	
	Receptacle, 40mm	
	Stack Height, Left	
	Guided, 12 Columns,	
	180 Circuits, Plated	
	Through Hole	
	Dimension 0.39mm,	
	Lead Free	
	Impact 100 Ohm	<u>765303046</u>
	5 Pair Mezzanine	
	Receptacle, 40mm	
	Stack Height, Left	
	Guided, 16 Columns,	
	240 Circuits, Plated	
	Through Hole	
	Dimension 0.39mm,	
	Lead-Free	

Impact 100 Ohm	<u>765303047</u>
5 Pair Mezzanine	
Receptacle, 40mm	
Stack Height, Left	
Guided, 14 Columns,	
210 Circuits, Plated	
Through Hole	
Dimension 0.39mm,	
Lead Free	
Impact 100 Ohm	<u>765305030</u>
5 Pair Mezzanine	
Receptacle, 38mm	
Stack Height, Right	
Guided, 10 Columns,	
150 Circuits, Plated	
Through Hole	
Dimension 0.39mm,	
Lead-Free	
Impact 100 Ohm	<u>765305032</u>
5 Pair Mezzanine	
Receptacle, 38mm	
Stack Height, Right	
Guided, 12 Columns,	
180 Circuits, Plated	
Through Hole	
Dimension 0.39mm,	
Lead-Free	
Impact 100 Ohm	<u>765305036</u>
5 Pair Mezzanine	
Receptacle, 38mm	
Stack Height, Right	
Guided, 16 Columns,	
240 Circuits, Plated	
Through Hole	
Dimension 0.39mm,	
Lead-Free	
Impact 100 Ohm	<u>765305040</u>
5 Pair Mezzanine	
Receptacle, 40mm	
Stack Height, Right	
Guided, 10 Columns,	
150 Circuits, Plated	
Through Hole	
Dimension 0.39mm,	
Lead-Free	
Impact 100 Ohm	<u>765305042</u>
5 Pair Mezzanine	
Receptacle, 40mm	
Stack Height, Right	
Guided, 12 Columns,	
180 Circuits, Plated	
Through Hole	
Dimension 0.39mm,	
Lead Free	
Impact 100 Ohm	<u>765305046</u>
5 Pair Mezzanine	
Receptacle, 40mm	
Stack Height, Right	
Guided, 16 Columns,	
240 Circuits, Plated	
Through Hole	
Dimension 0.39mm,	
Lead-Free	
Impact 100 Ohm	<u>765305047</u>
5 Pair Mezzanine	

Receptacle, 40mm
Stack Height, Right
Guided, 14 Columns,
210 Circuits, Plated
Through Hole
Dimension 0.39mm,
Lead Free

This document was generated on 06/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62100-2170](#)