

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0621003200

Status:

Active

Overview:

Application Tooling

Description:

IDT - Manual - Tool Kit

Documents:

RoHS Certificate of Compliance (PDF)


General	
Product Family	Application Tooling
Series	207126
Comments	Manual Standard Press Tool Kit for Milli-Grid 2.00mm
Function	Insulation Displacement (IDT)
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	IDT Hand Tool
UPC	800753942943
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-621003200-001, TM-621002200-001



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207126 Series

Use With

11316356

Application Tooling Description	FAQ Product #
Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 10 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	875681063
Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 10 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization	875681064

	Key and Locking Friction Ramp Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 10 Circuits, 0.38μm Gold (Au) Selective Plating, without Center Polarization	875681073
	Key, with Locking Friction Ramp Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 10 Circuits, 0.76μm Gold (Au) Selective Plating, without Center Polarization	875681074
	Key, with Locking Friction Ramp Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 12 Circuits, 0.38μm Gold (Au) Selective Plating, without Center Polarization	875681263
	Key and Locking Friction Ramp Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 12 Circuits, 0.76μm Gold (Au) Selective Plating, without Center Polarization	875681264
	Key and Locking Friction Ramp Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 12 Circuits, 0.38μm Gold (Au) Selective Plating, without Center Polarization	875681273
	Key, with Locking Friction Ramp Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 12 Circuits, 0.76μm Gold (Au) Selective Plating, without Center Polarization	875681274
	Key, with Locking Friction Ramp Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT,	875681443

Milli-Grid Cable-to- 875681444

Milli-Grid Cable-to-	<u>875681463</u>
----------------------	------------------

Milli-Grid Cable-to-	<u>875681464</u>
----------------------	------------------

MGrid IDT Rec W/ 875681483

LRmp .38AuLF
14Ckt

Milli-Grid Cable-to-	875681493
----------------------	-----------

Milli-Grid Cable-to-	875681494
----------------------	-----------

Milli-Grid Cable-to-	875681643
----------------------	-----------

Milli-Grid Cable-to-Board Receptacle,
Dual Row, IDT,
Lead-Free, 16
Circuits, 0.76μm
Gold (Au) Selective
Plating, with Center
Polarization Key,
without Locking

Friction Ramp
Milli-Grid Cable-to-
Board Receptacle,
Dual Row, IDT,
Lead-Free, 16
Circuits, 0.38μm
Gold (Au) Selective
Plating, without
Center Polarization
Key and Locking
Friction Ramp

Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 16 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp

MGrid IDT Rec W/ 875681683
LRmp .38AuLF
16Ckt

MGrid IDT Rec W/ 875681684
LRmp .76AuLF
16Ckt

Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 16 Circuits, 0.38μm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp

Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 16 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp

	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 20 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875682043</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 20 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875682044</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 20 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875682063</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 20 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875682064</u>
	MGrid IDT Rec W/ LRmp .38AuLF 20Ckt	<u>875682083</u>
	MGrid IDT Rec W/ LRmp .76AuLF 20Ckt	<u>875682084</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 20 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875682093</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 20 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key	<u>875682094</u>

	and Locking Friction Ramp	
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 22 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875682243</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 22 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875682244</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 22 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875682263</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 22 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875682264</u>
	MGrid IDT Rec W/ LRmp .38AuLF 22Ckt	<u>875682283</u>
	MGrid IDT Rec W/ LRmp .76AuLF 22Ckt	<u>875682284</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 22 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875682293</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 22 Circuits, 0.76µm Gold (Au) Selective Plating, with Center	<u>875682294</u>

	Polarization Key and Locking Friction Ramp	
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 24 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875682443</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 24 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875682444</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 24 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875682463</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 24 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875682464</u>
	MGrid IDT Rec W/ LRmp .38AuLF 24Ckt	<u>875682483</u>
	MGrid IDT Rec W/ LRmp .76AuLF 24Ckt	<u>875682484</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 24 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875682493</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 24 Circuits, 0.76µm Gold (Au) Selective	<u>875682494</u>

	Plating, with Center Polarization Key and Locking Friction Ramp	
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 26 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875682643</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 26 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875682644</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 26 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875682663</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 26 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875682664</u>
	MGrid IDT Rec W/ LRmp .38AuLF 26Ckt	<u>875682683</u>
	MGrid IDT Rec W/ LRmp .76AuLF 26Ckt	<u>875682684</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 26 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875682693</u>
	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 26 Circuits, 0.76µm	<u>875682694</u>

	Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 30 Circuits, 0.38µm	<u>875683043</u>
	Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 30 Circuits, 0.76µm	<u>875683044</u>
	Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 30 Circuits, 0.38µm	<u>875683063</u>
	Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 30 Circuits, 0.76µm	<u>875683064</u>
	Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	
	MGrid IDT Rec W/ LRmp .38AuLF 30Ckt	<u>875683083</u>
	MGrid IDT Rec W/ LRmp .76AuLF 30Ckt	<u>875683084</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 30 Circuits, 0.38µm	<u>875683093</u>
	Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 30	<u>875683094</u>

Circuits, 0.76μm
Gold (Au) Selective
Plating, with Center
Polarization Key
and Locking Friction
Ramp

Milli-Grid Cable-to- 875683443

Board Receptacle,
Dual Row, IDT,
Lead-Free, 34

Circuits, 0.38μm
Gold (Au) Selective
Plating, with Center
Polarization Key,
without Locking
Friction Ramp

Milli-Grid Cable-to- 875683444

Board Receptacle,
Dual Row, IDT,
Lead-Free, 34

Circuits, 0.76 μ m
Gold (Au) Selective
Plating, with Center
Polarization Key,
without Locking
Friction Ramp

Milli-Grid Cable-to-	<u>875683463</u>
----------------------	------------------

Board Receptacle,
Dual Row, IDT,
Lead-Free, 34

Circuits, 0.38 μ m
Gold (Au) Selective
Plating, without
Center Polarization
Key and Locking
Friction Ramp

Milli-Grid Cable-to- 875683464

Board Receptacle,
Dual Row, IDT,
Lead-Free, 34

Circuits, 0.76μm
Gold (Au) Selective
Plating, without
Center Polarization
Key and Locking
Friction Ramp

MGrid IDT Rec W/ 875683483

LRmp .38AuLF
34Ckt

MGrid IDT Rec W/ 875683484

LRmp .76AuLF
34Ckt

Milli-Grid Cable-to-	875683493
----------------------	-----------

Board Receptacle,
Dual Row, IDT,
Lead-Free, 34

Circuits, 0.38 μ m
Gold (Au) Selective
Plating, with Center
Polarization Key
and Locking Friction
Ramp

Milli-Grid Cable-to-	875683494
----------------------	-----------

Board Receptacle,
Dual Row, IDT,

	Lead-Free, 34 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp MGrid IDT Rec / 875683643 PolKey .38AuLF 36Ckt MGrid IDT Rec / 875683644 PolKey .76AuLF 36Ckt MGrid IDT Rec O/ 875683663 PolKeyLRmp .38AuLF 36Ckt MGrid IDT Rec O/ 875683664 PolKeyLRmp .76AuLF 36Ckt MGrid IDT Rec W/ 875683694 PolKeyLRmp .76AuLF 36Ckt Milli-Grid Cable-to- 875684043 Board Receptacle, Dual Row, IDT, Lead-Free, 40 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp Milli-Grid Cable-to- 875684044 Board Receptacle, Dual Row, IDT, Lead-Free, 40 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp Milli-Grid Cable-to- 875684063 Board Receptacle, Dual Row, IDT, Lead-Free, 40 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp Milli-Grid Cable-to- 875684064 Board Receptacle, Dual Row, IDT, Lead-Free, 40 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp MGrid IDT Rec W/ 875684083 LRmp .38AuLF 40Ckt
--	--

	MGrid IDT Rec W/ LRmp .76AuLF 40Ckt	<u>875684084</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 40 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875684093</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 40 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875684094</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 44 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875684443</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 44 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875684444</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 44 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875684463</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 44 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875684464</u>

	MGrid IDT Rec W/ LRmp .38AuLF 44Ckt	<u>875684483</u>
	MGrid IDT Rec W/ LRmp .76AuLF 44Ckt	<u>875684484</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 44 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875684493</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 44 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875684494</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 50 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875685043</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 50 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key, without Locking Friction Ramp	<u>875685044</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 50 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp	<u>875685063</u>
	Milli-Grid Cable-to- Board Receptacle, Dual Row, IDT, Lead-Free, 50 Circuits, 0.76µm Gold (Au) Selective Plating, without Center Polarization	<u>875685064</u>

Key and Locking Friction Ramp	
MGrid IDT Rec W/ LRmp .38AuLF 50Ckt	<u>875685083</u>
MGrid IDT Rec W/ LRmp .76AuLF 50Ckt	<u>875685084</u>
Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 50 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875685093</u>
Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 50 Circuits, 0.76µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp	<u>875685094</u>

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62100-3200](#)