

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0621005110

Status:

Active

Overview:

Application Tooling

Description:

Backplane Insertion Tool for Signal Contact Insertion

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207123

See Tooling Specification (PDF) Above

Insertion

Global

Manual

applicationtooling@molex.com

Application Tooling

N/A

Insertion Hand Tool

800756778679

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

51.873/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-621005110, TM-622018699, TM-622022099



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

207123 Series

Use With

GbX I-Trac Backplane [75705](#) , [76015](#) , [76035](#)

Application Tooling Description	FAQ Product #
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Unguided, Dual End Walls, 11 Rows, 10 Columns, 220 Circuits, Mating Pin Length 5.70mm	757051124
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Unguided, Dual End Wall, 11 Rows, 5 Columns, 110 Circuits, Mating Pin Length 4.70mm	757051523
GbX I-Trac Vertical Header Module,	757051602

1.85mm by 3.70mm
Pitch, Unguided,
Open Ends, 11
Rows, 6 Columns,
132 Circuits, Mating
Pin Length 3.90mm
GbX I-Trac Vertical 757051604
Header Module,
1.85mm by 3.70mm
Pitch, Unguided,
Open Ends, 11
Rows, 6 Columns,
132 Circuits, Mating
Pin Length 5.70mm
GbX I-Trac Vertical 757051634
Header Module,
1.85mm by 3.70mm
Pitch, Unguided,
Right End Wall, 11
Rows, 6 Columns,
132 Circuits, Mating
Pin Length 5.70mm
GbX I-Trac Vertical 757051804
Header Module,
1.85mm by 3.70mm
Pitch, Unguided,
Open Ends, 11
Rows, 8 Columns,
176 Circuits, Mating
Pin Length 5.70mm
GbX I-Trac Vertical 757053103
Header Module,
1.85mm by 3.70mm
Pitch, Left Guide,
Right Open, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 4.70mm
GbX I-Trac Vertical 757053104
Header Module,
1.85mm by 3.70mm
Pitch, Left Guide,
Right Open, 11
Rows, 10 Columns,
220 Circuits, Mating
Pin Length 5.70mm
GbX I-Trac Vertical 757053824
Header Module,
1.85mm by 3.70mm
Pitch, Left Guide,
Right Open, 11
Rows, 8 Columns,
176 Circuits, Key
Orientation B, Mating
Pin Length 5.70mm
GbX I-Trac Vertical 757055103
Header Module,
1.85mm by 3.70mm
Pitch, Right Guide,
Left Open, 11 Rows,
10 Columns, 200
Circuits, Mating Pin
Length 4.70mm
GbX I-Trac Vertical 757055604
Header Module,

	1.85mm by 3.70mm Pitch, Right Guide, Left Open, 11 Rows, 6 Columns, 132 Circuits, Mating Pin Length 5.70mm GbX I-Trac Vertical 757055824 Header Module, 1.85mm by 3.70mm Pitch, Right Guide, Left Open, 11 Rows, 8 Columns, 176 Circuits, Mating Pin Length 5.70mm, Key Orientation B GbX I-Trac Vertical 757057604 Header Module, 1.85mm by 3.70mm Pitch, Left Guide, Right Endwall, 11 Rows, 6 Columns, 132 Circuits, Mating Pin Length 5.70mm GbX I-Trac Vertical 757059605 Header Module, 1.85mm by 3.70mm Pitch, Right Guide, Left Endwall, 11 Rows, 6 Columns, 132 Circuits, Staggered Mating Pin Length 4.70mm & 5.70mm GbX I-Trac Vertical 760151102 Header Module, 1.85mm by 3.70mm Pitch, Unguided, Open Ends, 7 Rows, 10 Columns, 140 Circuits, Mating Pin Length 3.90mm GbX I-Trac Vertical 760151103 Header Module, 1.85mm by 3.70mm Pitch, Unguided, Open Ends, 7 Rows, 10 Columns, 140 Circuits, Mating Pin Length 4.70mm GbX I-Trac Vertical 760151104 Header Module, 1.85mm by 3.70mm Pitch, Unguided, Open Ends, 7 Rows, 10 Columns, 140 Circuits, Mating Pin Length 5.70mm GbX I-Trac Vertical 760151403 Header Module, 1.85mm by 3.70mm Pitch, Unguided, Open Ends, 7 Rows, 4 Columns, 56 Circuits, Mating Pin Length 4.70mm	
--	--	--

GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Unguided, Open Ends, 7 Rows, 4 Columns, 56 Circuits, Mating Pin Length 5.70mm	760151404
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Unguided, Open Ends, 7 Rows, 6 Columns, 84 Circuits, Mating Pin Length 3.90mm	760151602
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Unguided, Open Ends, 7 Rows, 6 Columns, 84 Circuits, Staggered Mating Pin Length 4.70mm & 5.70mm, Lead-Free	760151605
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Left Guide, Right Open, 7 Rows, 10 Columns, 140 Circuits, Mating Pin Length 4.70mm, Lead-Free	760153103
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Left Guide, Right Open, 7 Rows, 10 Columns, 140 Circuits, Mating Pin Length 5.70mm, Lead-Free	760153104
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Left Guide, Right Open, 7 Rows, 4 Columns, 56 Circuits, Mating Pin Length 3.90mm, Lead-Free	760153402
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Left Guide, Right Open, 7 Rows, 4 Columns, 56 Circuits, Mating Pin Length 4.70mm, Lead-Free	760153403
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm	760155103

Pitch, Right Guide,
Left Open, 7 Rows,
10 Columns, 140
Circuits, Mating Pin
Length 4.70mm,
Lead-Free
GbX I-Trac Vertical [760155104](#)
Header Module,
1.85mm by 3.70mm
Pitch, Right Guide,
Left Open, 7 Rows,
10 Columns, 140
Circuits, Mating Pin
Length 5.70mm,
Lead-Free
GbX I-Trac Vertical [760155402](#)
Header Module,
1.85mm by 3.70mm
Pitch, Right Guide,
Left Open, 7 Rows, 4
Columns, 56 Circuits,
Mating Pin Length
3.90mm, Lead-Free
GbX I-Trac Vertical [760155403](#)
Header Module,
1.85mm by 3.70mm
Pitch, Right Guide,
Left Open, 7 Rows, 4
Columns, 56 Circuits,
Mating Pin Length
4.70mm, Lead-Free
GbX I-Trac Vertical [760155605](#)
Header Module,
1.85mm by 3.70mm
Pitch, Right Guide,
Left Open, 7 Rows, 6
Columns, 84 Circuits,
Staggered Mating
Pin Length 4.70mm
& 5.70mm, Lead-
Free

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62100-5110](#)