

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622011101

Status:

Active

Overview:

Application Tooling

Description:

Insertion Module for Advanced Mate Signal Header, 6-Row by 11-Wide, 20.00mm


Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Press-Fit Insertion Tool
UPC	800754028646
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-622011101, TM-622010999



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per	
-ED/01/2018 (15	
January 2018)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit	Contact US
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207123 Series

Use With
VHDM Board-to-Board Backplane Header
74057 , 74058 , 74059

Application Tooling Description	FAQ Product #
VHDM Single-Ended Board-to-Board Backplane Header, 2.00mm Pitch, Vertical, 6-Rows, Open Signal Module, 60 Circuits, 10 Columns, Pin Length 4.75mm, 0.76µm Gold Plating. Series:74074 Enables designers to create custom loaded connectors utilizing standard pin	740571001

lengths 4.25, 4.75,
5.15 and 6.25mm
VHDM Single-
Ended Board-to-
Board Backplane
Header, 2.00mm
Pitch, Vertical, 6-
Rows, Open Signal
Module, 60 Circuits,
10 Columns, Pin
Length 5.15mm,
0.76µm Gold Plating.
Series:74074

740571004

Enables designers to create custom loaded connectors utilizing standard pin lengths 4.25, 4.75, 5.15 and 6.25mm

VHDM Single-Ended Board-to-Board Backplane Header, 2.00mm Pitch, Vertical, 6-Rows, Open Signal Module, 60 Circuits, 10 Columns, Pin Length 4.75mm, 0.76µm Gold (Au) Plating, Series:74074

740579001

Enables designers to create custom loaded connectors utilizing standard pin lengths 4.25, 4.75, 5.15 and 6.25mm

VHDM Single-Ended Board-to-Board Backplane Header, 2.00mm Pitch, Vertical, 6-Rows, Open Signal Module, 60 Circuits, 10 Columns, Pin Length 5.15mm, 1.27μm Gold (Au) Plating, Series:74074

740579009

Enables designers to create custom loaded connectors utilizing standard pin lengths 4.25, 4.75, 5.15 and 6.25mm

VHDM Single-Ended 740581002
Board-to-Board
Backplane Header,
2.00mm Pitch,
Vertical, 6 Rows,
Pin End Version, 60
Circuits, 10 Columns,
Pin Length 6.25mm
VHDM BP 6 ROW 740589001
SIG END ASSY 10
COL

740589001

VHDM Single-Ended 740591001
Board-to-Board
Backplane Header,
2.00mm Pitch,
Vertical, 6 Rows,
Guide Pin Signal
Module, Shield End
Version, 60 Circuits,
10 Columns, Pin
Length 4.75mm
VHDM Single-Ended 740591002
Board-to-Board
Backplane Header,
2.00mm Pitch,
Vertical, 6 Rows,
Guide Pin Signal
Module, Shield End
Version, 60 Circuits,
10 Columns, Pin
Length 6.25mm
VHDM Single-Ended 740599001
Board-to-Board
Backplane Header,
2.00mm Pitch,
Vertical, 6 Rows,
Guide Pin Signal
Module, Shield End
Version, 60 Circuits,
10 Columns, Pin
Length 4.75mm

This document was generated on 02/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-1101](#)