

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018640

Status:

Active

Overview:

Application Tooling

Description:

Backplane Module Installation Press-In Tool

Documents:

RoHS Certificate of Compliance (PDF)


General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	800756930626
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-622018640-001, TM-622018799-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207123 Series

Use With

Impact Backplane Signal Module, 76155 Series

Application Tooling Description	FAQ Product #
Impact 100 Ohm 4 Pair Vertical Backplane Header, Unguided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead Free	1712941104
Impact 100 Ohm 4 Pair Vertical Backplane Header, Unguided, Open Endwall, 10 Columns, 120 Circuits, Pin Length	1712941105

	5.50mm, Plated Through Hole Dimension 0.46mm, Lead Free Impact 100 Ohm 1712941108 4 Pair Vertical Backplane Header, Unguided, Open Endwall, 10 Columns, 120 Circuits, Pin Length
	5.50mm, Plated Through Hole Dimension 0.39mm, Lead Free Impact 100 Ohm 1712941118 4 Pair Vertical Backplane Header, Unguided, Left Endwall, 10 Columns, 120 Circuits, Pin Length
	5.50mm, Plated Through Hole Dimension 0.39mm, Lead Free Impact 100 Ohm 1712941125 4 Pair Vertical Backplane Header, Unguided, Dual Endwall, 10 Columns, 120 Circuits, Pin Length
	5.50mm, Plated Through Hole Dimension 0.46mm, Matte Tin, 0.254µm Gold Impact 100 Ohm 1712941137 4 Pair Vertical Backplane Header, Unguided, Right Endwall, 10 Columns, 120 Circuits, Pin Length
	4.90mm, Plated Through Hole Dimension 0.39mm, Matte Tin, 0.254µm Gold Impact 100 Ohm 1712941138 4 Pair Vertical Backplane Header, Unguided, Right Endwall, 10 Columns, 120 Circuits, Pin Length
	5.50mm, Plated Through Hole Dimension 0.39mm, Lead Free Impact 100 Ohm 1712943108 4 Pair Vertical Backplane Header, Left Guided,

Open Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead Free Impact 100 Ohm	<u>1712945108</u>
4 Pair Vertical Backplane Header, Right Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead Free Impact 100 Ohm	<u>761551103</u>
4 Pair Vertical Backplane Header, Unguided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761551104</u>
4 Pair Vertical Backplane Header, Unguided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761551105</u>
4 Pair Vertical Backplane Header, Unguided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761551106</u>
4 Pair Vertical Backplane Header, Unguided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761551107</u>
4 Pair Vertical Backplane Header,	

	Unguided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm 761551108 4 Pair Vertical Backplane Header, Unguided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm 761551113 4 Pair Vertical Backplane Header, Unguided, Left Endwall, 10 Columns, 120 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm 761551114 4 Pair Vertical Backplane Header, Unguided, Left Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm 761551115 4 Pair Vertical Backplane Header, Unguided, Left Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm 761551116 4 Pair Vertical Backplane Header, Unguided, Left Endwall, 10 Columns, 120 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm 761551117 4 Pair Vertical	
--	---	--

	Backplane Header, Unguided, Left Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>761551118</u> 4 Pair Vertical
	Backplane Header, Unguided, Left Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>761551123</u> 4 Pair Vertical
	Backplane Header, Unguided, Dual Endwall, 10 Columns, 120 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761551124</u> 4 Pair Vertical
	Backplane Header, Unguided, Dual Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761551125</u> 4 Pair Vertical
	Backplane Header, Unguided, Dual Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761551126</u> 4 Pair Vertical
	Backplane Header, Unguided, Dual Endwall, 10 Columns, 120 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free

	Impact 100 Ohm	<u>761551127</u>
	4 Pair Vertical	
	Backplane Header,	
	Unguided, Dual	
	Endwall, 10	
	Columns, 120	
	Circuits, Pin Length	
	4.90mm, Plated	
	Through Hole	
	Dimension 0.39mm,	
	Lead-Free	
	Impact 100 Ohm	<u>761551128</u>
	4 Pair Vertical	
	Backplane Header,	
	Unguided, Dual	
	Endwall, 10	
	Columns, 120	
	Circuits, Pin Length	
	5.50mm, Plated	
	Through Hole	
	Dimension 0.39mm,	
	Lead-Free	
	Impact 100 Ohm	<u>761551133</u>
	4 Pair Vertical	
	Backplane Header,	
	Unguided, Right	
	Endwall, 10	
	Columns, 120	
	Circuits, Pin Length	
	4.50mm, Plated	
	Through Hole	
	Dimension 0.46mm,	
	Lead-Free	
	Impact 100 Ohm	<u>761551134</u>
	4 Pair Vertical	
	Backplane Header,	
	Unguided, Right	
	Endwall, 10	
	Columns, 120	
	Circuits, Pin Length	
	4.90mm, Plated	
	Through Hole	
	Dimension 0.46mm,	
	Lead-Free	
	Impact 100 Ohm	<u>761551135</u>
	4 Pair Vertical	
	Backplane Header,	
	Unguided, Right	
	Endwall, 10	
	Columns, 120	
	Circuits, Pin Length	
	5.50mm, Plated	
	Through Hole	
	Dimension 0.46mm,	
	Lead-Free	
	Impact 100 Ohm	<u>761551136</u>
	4 Pair Vertical	
	Backplane Header,	
	Unguided, Right	
	Endwall, 10	
	Columns, 120	
	Circuits, Pin Length	
	4.50mm, Plated	
	Through Hole	

	Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>761551137</u> 4 Pair Vertical Backplane Header, Unguided, Right Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>761551138</u> 4 Pair Vertical Backplane Header, Unguided, Right Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>761553103</u> 4 Pair Vertical Backplane Header, Left Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761553104</u> 4 Pair Vertical Backplane Header, Left Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761553105</u> 4 Pair Vertical Backplane Header, Left Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761553106</u> 4 Pair Vertical Backplane Header, Left Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.50mm, Plated
--	--

Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761553107</u>
4 Pair Vertical Backplane Header, Left Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated	
Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761553108</u>
4 Pair Vertical Backplane Header, Left Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated	
Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761553118</u>
4 Pair Vertical Backplane Header, Left Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated	
Through Hole Dimension 0.39mm, Key Position A, Lead Free Impact 100 Ohm	<u>761553158</u>
4 Pair Vertical Backplane Header, Left Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated	
Through Hole Dimension 0.39mm, Key Position E, Lead Free Impact 100 Ohm	<u>761555103</u>
4 Pair Vertical Backplane Header, Right Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.50mm, Plated	
Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761555104</u>
4 Pair Vertical Backplane Header, Right Guided, Open Endwall,	

10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761555105</u>
4 Pair Vertical Backplane Header, Right Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761555106</u>
4 Pair Vertical Backplane Header, Right Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761555107</u>
4 Pair Vertical Backplane Header, Right Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761555108</u>
4 Pair Vertical Backplane Header, Right Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761555117</u>
4 Pair Vertical Backplane Header, Right Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Key Position A, Lead Free Impact 100 Ohm	<u>761555127</u>
4 Pair Vertical Backplane Header,	

	Right Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Key Position B, Lead Free Impact 100 Ohm <u>761555137</u> 4 Pair Vertical Backplane Header, Right Guided, Open Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Key Position C, Lead Free Impact 100 Ohm <u>761557103</u> 4 Pair Vertical Backplane Header, Left Guided, Right Endwall, 10 Columns, 120 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761557104</u> 4 Pair Vertical Backplane Header, Left Guided, Right Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761557105</u> 4 Pair Vertical Backplane Header, Left Guided, Right Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761557106</u> 4 Pair Vertical Backplane Header, Left Guided, Right Endwall, 10 Columns, 120 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	
--	---	--

	Impact 100 Ohm	<u>761557107</u>
	4 Pair Vertical	
	Backplane Header,	
	Left Guided,	
	Right Endwall,	
	10 Columns, 120	
	Circuits, Pin Length	
	4.90mm, Plated	
	Through Hole	
	Dimension 0.39mm,	
	Lead-Free	
	Impact 100 Ohm	<u>761557108</u>
	4 Pair Vertical	
	Backplane Header,	
	Left Guided,	
	Right Endwall,	
	10 Columns, 120	
	Circuits, Pin Length	
	5.50mm, Plated	
	Through Hole	
	Dimension 0.39mm,	
	Lead-Free	
	Impact 100 Ohm	<u>761557118</u>
	4 Pair Vertical	
	Backplane Header,	
	Left Guided,	
	Right Endwall,	
	10 Columns, 120	
	Circuits, Pin Length	
	5.50mm, Plated	
	Through Hole	
	Dimension 0.39mm ,	
	Key Orientation A,	
	Lead-Free	
	Impact 100 Ohm	<u>761559103</u>
	4 Pair Vertical	
	Backplane Header,	
	Right Guided,	
	Left Endwall, 10	
	Columns, 120	
	Circuits, Pin Length	
	4.50mm, Plated	
	Through Hole	
	Dimension 0.46mm,	
	Lead-Free	
	Impact 100 Ohm	<u>761559104</u>
	4 Pair Vertical	
	Backplane Header,	
	Right Guided,	
	Left Endwall, 10	
	Columns, 120	
	Circuits, Pin Length	
	4.90mm, Plated	
	Through Hole	
	Dimension 0.46mm,	
	Lead-Free	
	Impact 100 Ohm	<u>761559105</u>
	4 Pair Vertical	
	Backplane Header,	
	Right Guided,	
	Left Endwall, 10	
	Columns, 120	
	Circuits, Pin Length	
	5.50mm, Plated	
	Through Hole	

Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761559106</u>
4 Pair Vertical Backplane Header, Right Guided, Left Endwall, 10 Columns, 120 Circuits, Pin Length 4.50mm, Plated Through Hole	
Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761559107</u>
4 Pair Vertical Backplane Header, Right Guided, Left Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole	
Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761559108</u>
4 Pair Vertical Backplane Header, Right Guided, Left Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated Through Hole	
Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761559114</u>
4 Pair Vertical Backplane Header, Right Guided, Left Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole	
Dimension 0.46mm, Key Orientation A, Lead-Free Impact 100 Ohm	<u>761559165</u>
4 Pair Vertical Backplane Header, Right Guided, Left Endwall, 10 Columns, 120 Circuits, Pin Length 5.50mm, Plated Through Hole	
Dimension 0.46mm, Key Position F, Lead Free	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8640](#)