

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: [0622018663](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Daughter Card Signal Module Assembly Press-In Tool for 6-Pair by 16-Column Assemblies

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Press-Fit Insertion Tool
UPC	883906116200
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-622018663, TM-622018799



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed REACH SVHC Not Contained Per - ED/108/2014 (17 Dec 2014) Halogen-Free Status Not Relevant For more information, please visit Contact US	China RoHS
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[207123](#) Series

Application Tooling Description	FAQ Product #
Impact 85 Ohm Plus 6 Pair Right-Angle Daughtercard, Unguided, 16 Columns, 288 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free	1705401026
Impact 85 Ohm Plus 6 Pair Right-Angle Daughtercard, left Guided, 16 Columns, 288 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free	1705403026
Impact 85 Ohm Plus 6 Pair Right-Angle Daughtercard, Right	1705405026

Guided, 16 Columns,
288 Circuits, Plated
Through Hole
Dimension 0.39mm,
Lead Free

Impact 100 Ohm 761501016

6 Pair Right-Angle
Daughtercard

Receptacle,

Unguided, 16

Columns, 288

Circuits, Plated

Through Hole

Dimension 0.46mm,

Lead-Free

Impact 100 Ohm 761501026

6 Pair Right-Angle

Daughtercard

Receptacle,

Unguided, 16

Columns, 288

Circuits, Plated

Through Hole

Dimension 0.39mm,

Lead-Free

Impact 100 Ohm 761503016

6 Pair Right-Angle

Daughtercard

Receptacle, Left

Guided, 16 Columns,

288 Circuits, Plated

Through Hole

Dimension 0.46mm,

Lead-Free

Impact 100 Ohm 761503026

6 Pair Right-Angle

Daughtercard

Receptacle, Left

Guided, 16 Columns,

288 Circuits, Plated

Through Hole

Dimension 0.39mm,

Lead-Free

Impact 100 Ohm 761505016

6 Pair Right-Angle

Daughtercard

Receptacle, Right

Guided, 16 Columns,

288 Circuits, Plated

Through Hole

Dimension 0.46mm,

Lead-Free

Impact 100 Ohm 761505026

6 Pair Right-Angle

Daughtercard

Receptacle, Right

Guided, 16 Columns,

288 Circuits, Plated

Through Hole

Dimension 0.39mm,

Lead-Free

Impact 100 Ohm 761505126

6 Pair Right-Angle

Daughtercard

Receptacle, Right

Guided, 16 Columns,
288 Circuits, Plated
Through Hole
Dimension 0.39mm,
Polarizing Key
Position A, Lead-
Free

Impact 100 Ohm 761505326

6 Pair Right-Angle
Daughtercard
Receptacle, Right
Guided, 16 Columns,
288 Circuits, Plated
Through Hole
Dimension 0.39mm,
Polarizing Key
Position C, Lead-
Free

Impact 100 Ohm 765601607

6 Pair RAM Right-
Angle Header,
Unguided, Open
Endwall, 16
Columns, 288
Circuits, Pin Length
4.90mm, Plated
Through Hole
Dimension 0.39mm,
Lead-Free

Impact 100 Ohm 765601608

6 Pair RAM Right-
Angle Header,
Unguided, Open
Endwall, 16
Columns, 288
Circuits, Pin Length
5.50mm, Plated
Through Hole
Dimension 0.39mm,
Lead-Free

Impact 100 Ohm 765601627

6 Pair RAM Right-
Angle Header,
Unguided, Dual
Endwall, 16
Columns, 288
Circuits, Pin Length
4.90mm, Plated
Through Hole
Dimension 0.39mm,
Lead-Free

Impact 100 Ohm 765603607

6 Pair RAM Right-
Angle Header,
Left Guided,
Open Endwall,
16 Columns, 288
Circuits, Pin Length
4.90mm, Plated
Through Hole
Dimension 0.39mm,
Lead-Free

Impact 100 Ohm 765603608

6 Pair RAM Right-
Angle Header,

Left Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>765605607</u>
6 Pair RAM Right- Angle Header, Right Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>765605608</u>
6 Pair RAM Right- Angle Header, Right Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>765607607</u>
6 Pair RAM Right- Angle Header, Left Guided, Right Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>765607608</u>
6 Pair RAM Right- Angle Header, Left Guided, Right Endwall, 16 Columns, 288 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8663](#)