

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018664

Status:

Active

Overview:

Application Tooling

Description:

Backplane Module Installation Press-In Tool for 6 Pair by 16 Column Assemblies

Documents:

RoHS Certificate of Compliance (PDF)


General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	883906116316
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-622018664-001, TM-622018799-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Relevant	
REACH SVHC	
Not Relevant	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Relevant

Search Parts in this Series

207123 Series

Use With

Impact Backplane Signal Module 76145

Application Tooling Description	FAQ Product #
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Matte Tin, 0.254µm Gold	1712981604
Impact 100 Ohm 6 Pair Vertical Backplane Header, Unguided, Open Endwall, 16 Columns, 288 Circuits, Pin Length	1712981607

	4.90mm, Plated Through Hole Dimension 0.39mm, Matte Tin, 0.254µm Gold Impact 100 Ohm <u>761451603</u> 6 Pair Vertical Backplane Header, Unguided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761451604</u> 6 Pair Vertical Backplane Header, Unguided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761451605</u> 6 Pair Vertical Backplane Header, Unguided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761451606</u> 6 Pair Vertical Backplane Header, Unguided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>761451607</u> 6 Pair Vertical Backplane Header, Unguided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>761451608</u> 6 Pair Vertical Backplane Header, Unguided, Open Endwall, 16
--	---

Columns, 288 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761451613</u>
6 Pair Vertical Backplane Header, Unguided, Left Endwall, 16 Columns, 288 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761451614</u>
6 Pair Vertical Backplane Header, Unguided, Left Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761451615</u>
6 Pair Vertical Backplane Header, Unguided, Left Endwall, 16 Columns, 288 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761451616</u>
6 Pair Vertical Backplane Header, Unguided, Left Endwall, 16 Columns, 288 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761451617</u>
6 Pair Vertical Backplane Header, Unguided, Left Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761451618</u>

	Endwall, 16 Columns, 288 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>761451623</u> 6 Pair Vertical Backplane Header, Unguided, Dual Endwall, 16 Columns, 288 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761451624</u> 6 Pair Vertical Backplane Header, Unguided, Dual Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761451625</u> 6 Pair Vertical Backplane Header, Unguided, Dual Endwall, 16 Columns, 288 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761451626</u> 6 Pair Vertical Backplane Header, Unguided, Dual Endwall, 16 Columns, 288 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>761451627</u> 6 Pair Vertical Backplane Header, Unguided, Dual Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>761451628</u> 6 Pair Vertical Backplane Header,	
--	--	--

Unguided, Dual
Endwall, 16
Columns, 288
Circuits, Pin Length
5.50mm, Plated
Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761451633
6 Pair Vertical
Backplane Header,
Unguided, Right
Endwall, 16
Columns, 288
Circuits, Pin Length
4.50mm, Plated
Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761451634
6 Pair Vertical
Backplane Header,
Unguided, Right
Endwall, 16
Columns, 288
Circuits, Pin Length
4.90mm, Plated
Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761451635
6 Pair Vertical
Backplane Header,
Unguided, Right
Endwall, 16
Columns, 288
Circuits, Pin Length
5.50mm, Plated
Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761451636
6 Pair Vertical
Backplane Header,
Unguided, Right
Endwall, 16
Columns, 288
Circuits, Pin Length
4.50mm, Plated
Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761451637
6 Pair Vertical
Backplane Header,
Unguided, Right
Endwall, 16
Columns, 288
Circuits, Pin Length
4.90mm, Plated
Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761451638
6 Pair Vertical

	Backplane Header, Unguided, Right Endwall, 16 Columns, 288 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>761453603</u> 6 Pair Vertical
	Backplane Header, Left Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761453604</u> 6 Pair Vertical
	Backplane Header, Left Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761453605</u> 6 Pair Vertical
	Backplane Header, Left Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761453606</u> 6 Pair Vertical
	Backplane Header, Left Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>761453607</u> 6 Pair Vertical
	Backplane Header, Left Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free

	Impact 100 Ohm	<u>761453608</u>
	6 Pair Vertical	
	Backplane Header,	
	Left Guided,	
	Open Endwall,	
	16 Columns, 288	
	Circuits, Pin Length	
	5.50mm, Plated	
	Through Hole	
	Dimension 0.39mm,	
	Lead-Free	
	Impact 100 Ohm	<u>761453614</u>
	6 Pair Vertical	
	Backplane Header,	
	Left Guided,	
	Open Endwall,	
	16 Columns, 288	
	Circuits, Pin Length	
	4.90mm, Plated	
	Through Hole	
	Dimension 0.46mm,	
	Keying Orientation A,	
	Lead-Free	
	Impact 100 Ohm	<u>761453667</u>
	6 Pair Vertical	
	Backplane Header,	
	Left Guided,	
	Open Endwall,	
	16 Columns, 288	
	Circuits, Pin Length	
	4.90mm, Plated	
	Through Hole	
	Dimension 0.39mm ,	
	Keying Orientation F,	
	Lead-Free	
	Impact 100 Ohm	<u>761455603</u>
	6 Pair Vertical	
	Backplane Header,	
	Right Guided,	
	Open Endwall,	
	16 Columns, 288	
	Circuits, Pin Length	
	4.50mm, Plated	
	Through Hole	
	Dimension 0.46mm,	
	Lead-Free	
	Impact 100 Ohm	<u>761455604</u>
	6 Pair Vertical	
	Backplane Header,	
	Right Guided,	
	Open Endwall,	
	16 Columns, 288	
	Circuits, Pin Length	
	4.90mm, Plated	
	Through Hole	
	Dimension 0.46mm,	
	Lead-Free	
	Impact 100 Ohm	<u>761455605</u>
	6 Pair Vertical	
	Backplane Header,	
	Right Guided,	
	Open Endwall,	
	16 Columns, 288	
	Circuits, Pin Length	
	5.50mm, Plated	

Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761455606</u>
6 Pair Vertical Backplane Header, Right Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.50mm, Plated	
Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761455607</u>
6 Pair Vertical Backplane Header, Right Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated	
Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761455608</u>
6 Pair Vertical Backplane Header, Right Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 5.50mm, Plated	
Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761455614</u>
6 Pair Vertical Backplane Header, Right Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated	
Through Hole Dimension 0.46mm , Keying Orientation A, Lead-Free Impact 100 Ohm	<u>761455617</u>
6 Pair Vertical Backplane Header, Right Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated	
Through Hole Dimension 0.39mm , Keying Orientation A, Lead-Free Impact 100 Ohm	<u>761457603</u>
6 Pair Vertical Backplane Header, Left Guided, Right Endwall,	

16 Columns, 288 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761457604</u>
6 Pair Vertical Backplane Header, Left Guided, Right Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761457605</u>
6 Pair Vertical Backplane Header, Left Guided, Right Endwall, 16 Columns, 288 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761457606</u>
6 Pair Vertical Backplane Header, Left Guided, Right Endwall, 16 Columns, 288 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761457607</u>
6 Pair Vertical Backplane Header, Left Guided, Right Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761457608</u>
6 Pair Vertical Backplane Header, Left Guided, Right Endwall, 16 Columns, 288 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761457636</u>

	Right Endwall, 16 Columns, 288 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Polarizing Key Position C, Lead Free Impact 100 Ohm <u>761459603</u> 6 Pair Vertical Backplane Header, Right Guided, Left Endwall, 16 Columns, 288 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761459604</u> 6 Pair Vertical Backplane Header, Right Guided, Left Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761459605</u> 6 Pair Vertical Backplane Header, Right Guided, Left Endwall, 16 Columns, 288 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm <u>761459606</u> 6 Pair Vertical Backplane Header, Right Guided, Left Endwall, 16 Columns, 288 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm <u>761459607</u> 6 Pair Vertical Backplane Header, Right Guided, Left Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free
--	--

Impact 100 Ohm	<u>761459608</u>
6 Pair Vertical	
Backplane Header,	
Right Guided,	
Left Endwall, 16	
Columns, 288	
Circuits, Pin Length	
5.50mm, Plated	
Through Hole	
Dimension 0.39mm,	
Lead-Free	
Impact 100 Ohm	<u>761459616</u>
6 Pair Vertical	
Backplane Header,	
Right Guided,	
Left Endwall, 16	
Columns, 288	
Circuits, Pin Length	
4.50mm, Plated	
Through Hole	
Dimension 0.39mm,	
Lead Free	

This document was generated on 06/25/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8664](#)