

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018676

Status:

Active

Overview:

Application Tooling

Description:

Press-In Tool for Backplane Module

Documents:


RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Press-Fit Insertion Tool
UPC	883906297190
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical	
Net Weight	116.320/g

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-622018676-001, TM-622018799-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207123 Series

Use With

Impact Vertical Header 76055

Application Tooling Description	FAQ Product #
Impact 100 Ohm 4 Pair Vertical Backplane Header, Unguided, Open Endwall, 8 Columns, 96 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Matte Tin, 0.254µm Gold	1712941804
Impact 100 Ohm 4 Pair Vertical Backplane Header, Unguided, Right Endwall, 8 Columns, 96 Circuits, Pin Length 4.90mm, Plated Through Hole	1712941837

Dimension 0.39mm, Matte Tin, 0.254µm Gold	
Impact 100 Ohm	<u>1712949817</u>
4 Pair Vertical Backplane Header, Right Guided, Endwall, 8 Columns, 96 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Polarizing Key Position A, 0.254µm Gold	
Impact 100 Ohm	<u>1712949837</u>
4 Pair Vertical Backplane Header, Right Guided, Endwall, 8 Columns, 96 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Polarizing Key Position C, 0.254µm Gold	
Impact 100 Ohm	<u>761551803</u>
4 Pair Vertical Backplane Header, Unguided, Open Endwall, 8 Columns, 96 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free	
Impact 100 Ohm	<u>761551804</u>
4 Pair Vertical Backplane Header, Unguided, Open Endwall, 8 Columns, 96 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free	
Impact 100 Ohm	<u>761551805</u>
4 Pair Vertical Backplane Header, Unguided, Open Endwall, 8 Columns, 96 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free	
Impact 100 Ohm	<u>761551806</u>
4 Pair Vertical Backplane Header, Unguided, Open Endwall, 8 Columns, 96 Circuits, Pin Length 4.50mm, Plated Through Hole	

Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761551807
4 Pair Vertical
Backplane Header,
Unguided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761551808
4 Pair Vertical
Backplane Header,
Unguided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761551813
4 Pair Vertical
Backplane Header,
Unguided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761551814
4 Pair Vertical
Backplane Header,
Unguided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761551815
4 Pair Vertical
Backplane Header,
Unguided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761551816
4 Pair Vertical
Backplane Header,
Unguided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761551817
4 Pair Vertical
Backplane Header,

Unguided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761551818
4 Pair Vertical
Backplane Header,
Unguided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761551823
4 Pair Vertical
Backplane Header,
Unguided, Dual
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761551824
4 Pair Vertical
Backplane Header,
Unguided, Dual
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761551825
4 Pair Vertical
Backplane Header,
Unguided, Dual
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761551826
4 Pair Vertical
Backplane Header,
Unguided, Dual
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761551827
4 Pair Vertical
Backplane Header,
Unguided, Dual
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole

Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761551828</u>
4 Pair Vertical Backplane Header, Unguided, Dual Endwall, 8 Columns, 96 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761551833</u>
4 Pair Vertical Backplane Header, Unguided, Right Endwall, 8 Columns, 96 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761551834</u>
4 Pair Vertical Backplane Header, Unguided, Right Endwall, 8 Columns, 96 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761551835</u>
4 Pair Vertical Backplane Header, Unguided, Right Endwall, 8 Columns, 96 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761551836</u>
4 Pair Vertical Backplane Header, Unguided, Right Endwall, 8 Columns, 96 Circuits, Pin Length 4.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761551837</u>
4 Pair Vertical Backplane Header, Unguided, Right Endwall, 8 Columns, 96 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761551838</u>
4 Pair Vertical Backplane Header,	

Unguided, Right
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761553803
4 Pair Vertical
Backplane Header,
Left Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761553804
4 Pair Vertical
Backplane Header,
Left Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761553805
4 Pair Vertical
Backplane Header,
Left Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761553806
4 Pair Vertical
Backplane Header,
Left Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761553807
4 Pair Vertical
Backplane Header,
Left Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761553808
4 Pair Vertical
Backplane Header,
Left Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole

Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761555803
4 Pair Vertical
Backplane Header,
Right Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761555804
4 Pair Vertical
Backplane Header,
Right Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761555805
4 Pair Vertical
Backplane Header,
Right Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761555806
4 Pair Vertical
Backplane Header,
Right Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761555807
4 Pair Vertical
Backplane Header,
Right Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761555808
4 Pair Vertical
Backplane Header,
Right Guided, Open
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761557803
4 Pair Vertical
Backplane Header,

Left Guided, Right
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761557804
4 Pair Vertical
Backplane Header,
Left Guided, Right
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761557805
4 Pair Vertical
Backplane Header,
Left Guided, Right
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761557806
4 Pair Vertical
Backplane Header,
Left Guided, Right
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761557807
4 Pair Vertical
Backplane Header,
Left Guided, Right
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761557808
4 Pair Vertical
Backplane Header,
Left Guided, Right
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761559803
4 Pair Vertical
Backplane Header,
Right Guided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.50mm,
Plated Through Hole

Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761559804
4 Pair Vertical
Backplane Header,
Right Guided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761559805
4 Pair Vertical
Backplane Header,
Right Guided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 761559806
4 Pair Vertical
Backplane Header,
Right Guided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761559807
4 Pair Vertical
Backplane Header,
Right Guided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761559808
4 Pair Vertical
Backplane Header,
Right Guided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 761559817
4 Pair Vertical
Backplane Header,
Right Guided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm ,
Key Orientation A,
Lead-Free
Impact 100 Ohm 761559827
4 Pair Vertical

Backplane Header,
Right Guided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm ,
Key Orientation B,
Lead-Free
Impact 100 Ohm 761559837
4 Pair Vertical
Backplane Header,
Right Guided, Left
Endwall, 8 Columns,
96 Circuits, Pin
Length 4.90mm,
Plated Through Hole
Dimension 0.39mm ,
Key Orientation C,
Lead-Free

This document was generated on 06/26/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8676](#)