

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018677

Status:

Active

Overview:

Application Tooling

Description:

Press-In Tool for Daughter Card Module

Documents:

RoHS Certificate of Compliance (PDF)


General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Press-Fit Insertion Tool
UPC	883906297213
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-622018677, TM-622018799



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207123 Series

Use With

Impact Daughtercard Signal Module Assembly [76160](#)

Application Tooling Description	FAQ Product #
Impact 85 Ohm Plus 4 Pair, Right-Angle Daughtercard, Unguided, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free	1703401038
Impact 85 Ohm Plus 4 Pair, Right-Angle Daughtercard, Left Guided, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free	1703403038
Impact 85 Ohm Plus 4 Pair, Right-	1703405038

Angle Daughtercard, Right Guided, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free Impact 100 Ohm	<u>761601008</u>
4 Pair Right-Angle Daughtercard Receptacle, Unguided, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761601038</u>
4 Pair Right-Angle Daughtercard Receptacle, Unguided, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761603008</u>
4 Pair Right-Angle Daughtercard Receptacle, Left Guided, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761603038</u>
4 Pair Right-Angle Daughtercard Receptacle, Left Guided, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>761605008</u>
4 Pair Right-Angle Daughtercard Receptacle, Right Guided, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>761605038</u>
4 Pair Right-Angle Daughtercard Receptacle, Right Guided, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>765001805</u>
4 Pair RAM Right- Angle Header, Unguided, Open Endwall, 8 Columns,	

96 Circuits, Pin
Length 5.50mm,
Plated Through Hole
Dimension 0.46mm,
Lead Free

Impact 100 Ohm	<u>765001807</u>
----------------	------------------

4 Pair RAM Right-Angle Header,

Unguided, Open
Endwall, 8 Columns,

96 Circuits, Pin
Length 4.90mm,

Plated Through Hole
Dimension 0.39mm,

Lead-Free

Impact 100 Ohm	<u>765001808</u>
----------------	------------------

4 Pair RAM Right-Angle Header,

Unguided, Open
Endwall, 8 Columns,

96 Circuits, Pin
Length 5.50mm,

Plated Through Hole
Dimension 0.39mm,

Lead Free

Impact 100 Ohm	<u>765001817</u>
----------------	------------------

4 Pair RAM Right-Angle Header,

Unguided, Left
Endwall, 8 Columns,

96 Circuits, Pin
Length 4.90mm,

Plated Through Hole
Dimension 0.39mm,

Lead-Free

Impact 100 Ohm	<u>765001827</u>
----------------	------------------

4 Pair RAM Right-Angle Header,

Unguided, Dual
Endwall, 8 Columns,

96 Circuits, Pin
Length 4.90mm,

Plated Through Hole
Dimension 0.39mm,

Lead-Free

Impact 100 Ohm	<u>765001828</u>
----------------	------------------

4 Pair RAM Right-Angle Header,

Unguided, Dual
Endwall, 8 Columns,

96 Circuits, Pin
Length 5.50mm,

Plated Through Hole
Dimension 0.39mm,

Lead-Free

Impact 100 Ohm	765001838
----------------	-----------

4 Pair RAM Right-Angle Header,

Angle Header,
Unguided, Right
Endwall, 8 Columns,

96 Circuits, Pin Length 5.50mm,

Plated Through Hole
Dimension 0.39mm.

Lead-Free

Impact 100 Ohm 4 Pair RAM Right- Angle Header, Left Guided, Open Endwall, 8 Columns, 96 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead Free	<u>765003805</u>
Impact 100 Ohm 4 Pair RAM Right- Angle Header, Left Guided, Open Endwall, 8 Columns, 96 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>765003807</u>
Impact 100 Ohm 4 Pair RAM Right- Angle Header, Right Guided, Open Endwall, 8 Columns, 96 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead Free	<u>765005805</u>
Impact 100 Ohm 4 Pair RAM Right- Angle Header, Right Guided, Open Endwall, 8 Columns, 96 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>765005807</u>
Impact 100 Ohm 4 Pair RAM Right- Angle Header, Right Guided, Open Endwall, 8 Columns, 96 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead Free	<u>765005808</u>
Impact 100 Ohm 4 Pair RAM Right- Angle Header, Left Guided, Right Endwall, 10 Columns, 96 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>765007807</u>
Impact 100 Ohm 4 Pair RAM Right- Angle Header, Left Guided, Right Endwall, 8 Columns,	<u>765007808</u>

96 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead Free Impact 100 Ohm	<u>765009808</u>
4 Pair RAM Right- Angle Header, Right Guided, Left Endwall, 8 Columns, 96 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead Free Impact 100 Ohm	<u>768501008</u>
4 Pair Right- Angle Orthogonal Daughtercard, Unguided, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>768501038</u>
4 Pair Right- Angle Orthogonal Daughtercard, Unguided, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>768503008</u>
4 Pair Right- Angle Orthogonal Daughtercard, Left Guide, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>768503038</u>
4 Pair Right- Angle Orthogonal Daughtercard, Left Guide, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free Impact 100 Ohm	<u>768505008</u>
4 Pair Right- Angle Orthogonal Daughtercard, Right Guide, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free Impact 100 Ohm	<u>768505038</u>

96 Circuits, Plated
Through Hole
Dimension 0.39mm,
Lead-Free

This document was generated on 02/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8677](#)