

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018779

Status:

Active

Overview:

Application Tooling

Description:

Press-in-Tool for Daughter Card Signal Module, 2-Pair by 16-Column Assemblies

Documents:

RoHS Certificate of Compliance (PDF)


General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	884982113879
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-622018779, TM-622018799



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207123 Series

Use With

Impact Daughtercard Signal Module Assembly 76460 . Impact RAM Signal Module Assembly 76450 2-Pair by 16 Column Assemblies

Application Tooling Description	FAQ Product #
Impact 100 Ohm 2 Pair Right-Angle Male Header, Unguided, Open Endwall, 16 Columns, 96 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	764501607
Impact 100 Ohm 2 Pair Right-Angle Male Header, Unguided, Open Endwall, 16 Columns, 96 Circuits,	764501608

Pin Length 5.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free

Impact 100 Ohm 764501627

2 Pair Right-Angle
Male Header,
Unguided, Dual
Endwall, 16

Columns, 96 Circuits,
Pin Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead Free

Impact 100 Ohm 764501637

2 Pair Right-Angle
Male Header,
Unguided, Right
Endwall, 16

Columns, 96 Circuits,
Pin Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free

Impact 100 Ohm 764503607

2 Pair Right-Angle
Male Header,
Left Guided,
Open Endwall, 16

Columns, 96 Circuits,
Pin Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free

Impact 100 Ohm 764503608

2 Pair Right-Angle
Male Header,
Left Guided,
Open Endwall, 16

Columns, 96 Circuits,
Pin Length 5.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free

Impact 100 Ohm 764505607

2 Pair Right-Angle
Male Header,
Right Guided,
Open Endwall, 16

Columns, 96 Circuits,
Pin Length 4.90mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free

Impact 100 Ohm 764505608

2 Pair Right-Angle
Male Header,
Right Guided,
Open Endwall, 16

Columns, 96 Circuits,
Pin Length 5.50mm,
Plated Through Hole
Dimension 0.39mm,
Lead-Free

	Impact 100 Ohm	<u>764507607</u>
	2 Pair Right-Angle	
	Male Header,	
	Left Guided,	
	Right Endwall, 16	
	Columns, 96 Circuits,	
	Pin Length 4.90mm,	
	Plated Through Hole	
	Dimension 0.39mm,	
	Lead-Free	
	Impact 100 Ohm	<u>764509607</u>
	2 Pair Right-Angle	
	Male Header, Right	
	Guided, Left Endwall,	
	16 Columns, 96	
	Circuits, Pin Length	
	4.90mm, Plated	
	Through Hole	
	Dimension 0.39mm,	
	Lead-Free	
	Impact 100 Ohm	<u>764601016</u>
	2 Pair Right-Angle	
	Daughtercard	
	Receptacle,	
	Unguided, 16	
	Columns, 96 Circuits,	
	Plated Through Hole	
	Dimension 0.46mm,	
	Lead-Free	
	Impact 100 Ohm	<u>764601026</u>
	2 Pair Right-Angle	
	Daughtercard	
	Receptacle,	
	Unguided, 16	
	Columns, 96 Circuits,	
	Plated Through Hole	
	Dimension 0.39mm,	
	Lead-Free	
	Impact 100 Ohm	<u>764603016</u>
	2 Pair Right-Angle	
	Daughtercard	
	Receptacle, Left	
	Guided, 16 Columns,	
	96 Circuits, Plated	
	Through Hole	
	Dimension 0.46mm,	
	Lead-Free	
	Impact 100 Ohm	<u>764603026</u>
	2 Pair Right-Angle	
	Daughtercard	
	Receptacle, Left	
	Guided, 16 Columns,	
	96 Circuits, Plated	
	Through Hole	
	Dimension 0.39mm,	
	Lead-Free	
	Impact 100 Ohm	<u>764605016</u>
	2 Pair Right-Angle	
	Daughtercard	
	Receptacle, Right	
	Guided, 16 Columns,	
	96 Circuits, Plated	
	Through Hole	
	Dimension 0.46mm,	
	Lead-Free	

Impact 100 Ohm 2 Pair Right-Angle Daughtercard Receptacle, Right Guided, 16 Columns, 96 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764605026</u>
---	------------------

This document was generated on 02/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8779](#)