

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	<u>0639004500</u>
Status:	Active
Overview:	<u>Application Tooling</u>
Description:	FineAdjust Applicator for Insulation OD 1.30-1.85mm, 20-24 AWG Wire

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

General	
Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above, Terminals will accommodate the UL1007 wires
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	FineAdjust
Tool Type	Applicator
UPC	883906021825
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	4980.585/g
------------	------------

Material Info

Reference - Drawing Numbers

Application Tooling Documents	ATS-639004500-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900SP-001
-------------------------------	--



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207127 Series

Use With

Molax TM-3000: 638017200 , 638017300
 , Molax TM-4000: 638017600 , Molax
 TM-2000: 638008300 , 638008400 , and
 Most Industry Standard Presses or Wire
 Process Machines

Application Tooling Description

| FAQ
Product #

Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 20-24 AWG, Reel	<u>430300001</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel	<u>430300002</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au)	<u>430300003</u>

Plated Phosphor
Bronze Contact,
20-24 AWG, Reel
Micro-Fit 3.0 Crimp 430310001
Terminal, Male,
with Tin (Sn) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit 3.0 Crimp 430310002
Terminal, Male,
with 0.38µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit 3.0 Crimp 430310003
Terminal, Male,
with 0.76µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit TPA Crimp 430315003
Terminal, Male, with
Tin (Sn) Pre-plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit TPA Crimp 430315004
Terminal, Male,
with 0.38µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit TPA Crimp 430315005
Terminal, Male,
with 0.76µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit TPA Crimp 430315006
Terminal, Male, with
2.54µm Matte Tin
Plated Phosphor
Bronze Contact,
20-24 AWG, Reel
Micro-Fit 3.0 Crimp 457730001
Terminal, Female,
with Lubricant, with
Tin (Sn) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit 3.0 Crimp 457730003
Terminal, Female,
with Lubricant, with
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit 3.0 Crimp 457730053
Terminal, Female,

with Lubricant, with
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel

This document was generated on 07/28/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

63900-4500