

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0752372253

Status:

Active

Overview:

GbX Backplane Connector System

Description:

GbX 5 Pair Backplane Connector System, Left Guide Header, 250 Circuits, 25 Columns, Gold (Au) 0.76µm, Pin Length 3.55mm, Key Orientation E


Documents:

Drawing (PDF)

Product Specification PS-75221-999-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	Backplane Connectors
Series	75237
Application	Backplane
Application Tooling Documents	TM-622022099
Comments	Left Guide Header, Keying Position E, Left Guide Header, Keying Position E
Component Type	PCB Header
Overview	GbX Backplane Connector System
Product Name	GbX
UPC	822350177511
Physical	
Circuits (Loaded)	250
Circuits (maximum)	250
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Material - Plating Mating	Gold
Net Weight	15.413/kg
Number of Columns	25
Number of Pairs	5
Number of Rows	10
Orientation	Vertical
PC Tail Length	2.30mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.85mm
Pitch - Termination Interface	1.85mm
Polarized to PCB	No
Stackable	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	105°C
Electrical	
Current - Maximum per Contact	1.0A
Data Rate	8.0 Gbps
Real Signals (per 25mm)	135
Shield Type	Ground Plane Shield
Shielded	Yes



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

75237 Series

Mates With

75360 GbX Daughtercard

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Insertion Tool, 5-Pair by 25-Wide	622022050
Single Pin Repair Tool	622022090
Shield Removal Tool	622022100

Voltage - Maximum	120V AC (RMS)/DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-75221-999-001
Sales Drawing	SD-75237-210

This document was generated on 09/13/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

75237-2253