

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0643251023

Status:

Active

Overview:

CMC and CMX Sealed, Hybrid, Modular Connectors

Description:

CMC Blind Plug cavity 1.50mm



Documents:

Drawing (PDF)	Application Specification AS-64319-002-FR-001 (PDF)
Product Specification PS-64319-002-001 (PDF)	Application Specification AS-64319-002-SP-001 (PDF)
Application Specification AS-501820-001-001 (PDF)	Application Specification AS-98420-001-001 (PDF)
Application Specification AS-501820-001-JP-001 (PDF)	Application Specification AS-98420-001-CH-001 (PDF)
Application Specification AS-560065-001-001 (PDF)	Application Specification AS-98420-001-FR-001 (PDF)
Application Specification AS-560065-001-CH-001 (PDF)	Application Specification AS-98420-001-SP-001 (PDF)
Application Specification AS-560065-001-FR-001 (PDF)	Application Specification AS-98420-002-001 (PDF)
Application Specification AS-64318-002-001 (PDF)	Application Specification AS-98420-002-CH-001 (PDF)
Application Specification AS-64318-002-CH-001 (PDF)	Application Specification AS-98420-002-FR-001 (PDF)
Application Specification AS-64318-002-FR-001 (PDF)	Application Specification AS-98420-002-SP-001 (PDF)
Application Specification AS-64318-002-SP-001 (PDF)	Packaging Specification PK-64325-002-001 (PDF)
Application Specification AS-64319-002-001 (PDF)	Datasheet (PDF)
Application Specification AS-64319-002-CH-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Accessories
Series	64325
Application	Automotive
Component Type	Wire Plug
Overview	CMC and CMX Sealed, Hybrid, Modular Connectors
Product Name	CMC
UPC	883906127534

Physical

Circuits (Loaded)	0
Circuits (maximum)	0
Net Weight	0.098/g
Packaging Type	Carton

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-501820-001-001, AS-501820-001-JP-001, AS-560065-001-001, AS-560065-001-CH-001, AS-560065-001-FR-001, AS-64318-002-001, AS-64318-002-CH-001, AS-64318-002-FR-001, AS-64318-002-SP-001, AS-64319-002-001, AS-64319-002-CH-001, AS-64319-002-FR-001,
---------------------------	--

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Perfluorohexane-1-
sulphonic acid and its
salts
reaction mass of
2-ethylhexyl 10-
ethyl-4,4-dioct
Methylhexahydrophthalic
anhydride
Pyrene
Fluoranthene
Tris(4-nonylphenyl,
branched and linear)
phosphi
Boric acid
n-pentyl-
isopentylphthalate
1,2-
Benzenedicarboxylic
acid, dipentyl ester, br
diisohexyl phthalate
2-(2H-Benzotriazol-2-
yl)-4-(tert-butyl)-6-
(sec-b
2-(2H-Benzotriazol-2-
yl)-4,6-
ditertpentylphenol
2-ethylhexyl 10-
ethyl-4,4-dioctyl-7-
oxo-8-oxa-3,
Disodium-octaborate
C.I. Direct Black 38
Dibutyltin-dichloride
1,2-
Benzenedicarboxylic
acid, bis(3-
methylbutyl)

China RoHS

Packaging Specification
Product Specification
Sales Drawing

AS-64319-002-SP-001, AS-98420-001-001,
AS-98420-001-CH-001, AS-98420-001-FR-001,
AS-98420-001-SP-001, AS-98420-002-001,
AS-98420-002-CH-001, AS-98420-002-FR-001,
AS-98420-002-SP-001
PK-64325-002-001
PS-64319-002-001
SD-64325-002-001

Disodium 3,3'-[[1,1'-
Biphenyl]-4,4'-
Diylbis(Azo)
Octamethylcyclotetrasiloxane
Dodecamethylcyclohexasiloxane
Octanoic acid,
2,2,3,3,4,4,5,5,6,6,7,7,8,8,8-
pen
Benzo(ghi)perylene
bis(2-(2-
methoxyethoxy)ethyl)
ether
Phenanthrene
Fatty Acids, C16-18,
Lead Salts
Sulfurous Acid, Lead
Salt, Dibasic
Lead titanium
zirconium oxide
Pentalead-tetraoxide-
sulphate
Lead oxide sulfate
(Pb2O(SO4))
Lead
Cadmium-sulphide
Diboron-trioxide
Decabromodiphenylether
1,2-bis(2-
methoxyethoxy)ethane
bis(2-methoxyethyl)
ether
Boric acid, disodium
salt, hydrate
Tris(2-chloroethyl)
phosphate
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[64325](#) Series

Use With
CMC Connector [64318](#) , [64319](#) , [64320](#) ,
[64321](#) , [64326](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[64325-1023](#) [64325-1175](#) [64325-1196](#)