

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0673298020

Status:

Active

Overview:

USB Products and Solutions

Description:

Universal Serial Bus (USB) Shielded I/O Receptacle, Type A, Single Upright Right-Angle, Solder Tail Length 2.00mm, 3.65mm Beveled Metal Pins, PCB Thickness 1.60mm, Gold (Au) Flash, Lead-Free

Documents:


3D Model

Drawing (PDF)

3D Model (PDF)

Packaging Specification PK-67329-001-001 (PDF)

RoHS Certificate of Compliance (PDF)



Series image - Reference only

Agency Certification

UL

E29179

General

Product Family

Series

Application

Comments

Component Type

Overview

Product Name

Standard

Type

UPC

I/O Connectors

67329

Wire-to-Board

Standard Mount Type|Beveled Metal Pin Length: 3.65mm

Receptacle

USB Products and Solutions

USB

USB 2.0

A

822350416900

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Flammability

Gender

Lock to Mating Part

Material - Plating Mating

Material - Plating Termination

Mounting Style

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Ports

Surface Mount Compatible (SMC)

Termination Interface: Style

Waterproof / Dustproof

4

4

Black

94V-0

Female

Yes

Gold

Tin

Upright

1.937/g

4

Right Angle

2.00mm

Yes

Yes

1.60mm

Tray

No

N/A

1.40mm

0.102µm

2.540µm

Yes

Yes

1

Yes

Through Hole

No

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

67329 Series

Mates With

USB Type A Plug

Electrical

Current - Maximum per Contact	1.0A
Shield Type	Full Shield
Shielded	Yes

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Electrical Model Document	EE-67329-001-001
Packaging Specification	PK-67329-001-001
Sales Drawing	SD-67329-802-001

This document was generated on 08/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

67329-8020