


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0752374145](#)
Status: **Active**
Overview: [GbX Backplane Connector System](#)
Description: GbX 5 Pair Backplane Connector System, Right Guide Header, 100 Circuits, 10 Columns, Gold (Au) 0.76µm, Pin Length 5.55mm, Key Orientation D

Documents:
[3D Model](#) [Product Specification PS-75221-999-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E29179
General	
Product Family	Backplane Connectors
Series	75237
Application	Backplane
Application Tooling Documents	TM-622022099
Comments	Right Guide Header, Keying Position D, Right Guide Header, Keying Position D
Component Type	PCB Header
Overview	GbX Backplane Connector System
Product Name	GbX
UPC	822350177986
Physical	
Circuits (Loaded)	100
Circuits (maximum)	100
Color - Resin	Gray (Dark)
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA), Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Material - Resin	High Temperature Thermoplastic
Net Weight	8.663/g
Number of Columns	10
Number of Pairs	5
Number of Rows	10
Orientation	Vertical
PC Tail Length	2.30mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.85mm
Pitch - Termination Interface	1.85mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	No
Stackable	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	105°C
Termination Interface: Style	Through Hole - Compliant Pin



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[75237](#) Series

Mates With
[75360](#) GbX Daughtercard

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Insertion Tool, 5-Pair by 10-Wide	622022030
Insertion Tool, 5-Pair by 20-Wide	622022040
Single Pin Repair Tool	622022090
Shield Removal Tool	622022100

Electrical

Current - Maximum per Contact	1.0A
Data Rate	8.0 Gbps
Real Signals (per 25mm)	135
Shield Type	Ground Plane Shield
Shielded	Yes
Voltage - Maximum	120V AC (RMS)/DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Product Specification	PS-75221-999-001
Sales Drawing	SD-75237-410

This document was generated on 09/14/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

75237-4145