

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0752374234](#)
Status: **Active**
Overview: [GbX Backplane Connector System](#)
Description: GbX 5 Pair Backplane Connector System, Right Guide Header, 250 Circuits, 25 Columns, Gold (Au) 0.76µm, Pin Length 4.55mm, Key Orientation C

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-75221-999-001 \(PDF\)](#)

Agency Certification

UL E29179

General


Product Family Backplane Connectors
Series [75237](#)
Application Backplane
Application Tooling Documents TM-622022099
Comments Right Guide Header, Keying Position C, Right Guide Header, Keying Position C
Component Type PCB Header
Overview [GbX Backplane Connector System](#)
Product Name GbX
UPC 822350179355

Physical

Circuits (Loaded) 250
Circuits (maximum) 250
Durability (mating cycles max) 200
First Mate / Last Break No
Flammability 94V-0
Guide to Mating Part Yes
Keying to Mating Part Yes
Material - Plating Mating Gold
Net Weight 15.413/kg
Number of Columns 25
Number of Pairs 5
Number of Rows 10
Orientation Vertical
PC Tail Length 2.30mm
PCB Locator No
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Pitch - Mating Interface 1.85mm
Pitch - Termination Interface 1.85mm
Polarized to PCB No
Stackable Yes
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating 105°C

Electrical

Current - Maximum per Contact 1.0A
Data Rate 8.0 Gbps
Real Signals (per 25mm) 135
Shield Type Ground Plane Shield
Shielded Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[75237](#) Series

Mates With

[75360](#) GbX Daughtercard

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Tool, 5-Pair by 25-Wide	622022050
Single Pin Repair Tool	622022090
Shield Removal Tool	622022100

Voltage - Maximum	120V AC (RMS)/DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-75221-999-001
Sales Drawing	SD-75237-410

This document was generated on 09/17/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

75237-4234