

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0740571003

Status:


Active

Overview:

VHDM® Backplane Connector Systems

Description:

VHDM® Single-Ended Board-to-Board Backplane Header, 2.00mm Pitch, Vertical, 6-Rows, Open Signal Module, 60 Circuits, 10 Columns, Pin Length 4.25mm, 0.76µm Gold Plating. Series:74074 Enables designers to create custom loaded connectors utilizing standard pin lengths 4.25, 4.75, 5.15 and 6.25mm



Documents:	
3D Model	Packaging Specification PK-74057-003 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-74031-999 (PDF)	

Agency Certification	
UL	E29179
General	
Product Family	Backplane Connectors
Series	74057
Application	Backplane
Application Tooling Documents	TM-622010999
Comments	Open Header
Component Type	PCB Header
Overview	VHDM® Backplane Connector Systems
Product Name	VHDM®
UPC	800753014770
Physical	
Circuits (Loaded)	60
Circuits (maximum)	60
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	Beryllium Copper, High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	4.238/g
Number of Columns	10
Number of Pairs	Open Pin Field
Number of Rows	6
Orientation	Vertical
PC Tail Length	2.50mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.80mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	105°C

EU ELV
Not Relevant

EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - ED/21/2016 (20 June 2016)	
Halogen-Free Status Low-Halogen	

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant

Search Parts in this Series
74057 Series

Mates With
74030 VHDM® Board-to-Board
Daughtercard Receptacle

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
6-Row Pin and Shield Repair Tool	0622015800
Insertion Module for Advanced Mate Signal Header, 6-	0622020203

Termination Interface: Style	Through Hole - Compliant Pin	Row by 10-Wide, 20.00mm
Electrical		Insertion Module <u>0622020207</u>
Current - Maximum per Contact	2.0A	for Advanced Mate
Data Rate	3.125 Gbps	Signal Header, 6-
Shield Type	Ground Plane Shield	Row by 10-Wide, 20.00mm
Shielded	Yes	Signal Pin Inserter <u>0622015700</u>
Voltage - Maximum	120V AC (RMS)/DC	Repair Tool
Solder Process Data		6-Row Shield <u>0622016000</u>
Lead-freeProcess Capability	N/A	Extraction Tool
Material Info		Insertion Module <u>0622011101</u>
Reference - Drawing Numbers		for Advanced Mate
Packaging Specification	PK-74057-003	Signal Header, 6-
Product Specification	PS-74031-999	Row by 11-Wide, 20.00mm
Sales Drawing	SD-74057-002	

Note: HDM, HDM+, VHDM, VHDM-HSD and GbX are trademarks or registered trademarks of Amphenol TCS.

This document was generated on 09/30/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74057-1003](#)