

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0757830311

Status:


Active

Overview:

iPass Connector System

Description:

iPass I/O Surface Mount Receptacle, Right-Angle, Internal Assembly with Shell, 68 Circuit, 0.38µm Gold (Au), Surface Mount Option, Tail Length 1.96mm, Left Key



Series image - Reference only

Documents:

- [3D Model](#)
- [3D Model \(PDF\)](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-75783-001-001 \(PDF\)](#)
- [Application Specification AS-75783-001 \(PDF\)](#)
- [Packaging Specification PK-75783-002 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	I/O Connectors
Series	75783
Application	Wire-to-Board
Comments	Positive or passive latching cable available
Component Type	Receptacle
Electrical Model	Yes
Overview	iPass Connector System
Product Name	iPass, Mini Multi-Lane, PCI Express
Type	N/A
UPC	822350092692

Physical

Circuits (Loaded)	68
Circuits (maximum)	68
Color - Resin	Black
Durability (mating cycles max)	50
Flammability	94V-0
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper-Nickel-Zinc, High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	4.664/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	1.96mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Embossed Tape on Reel
Panel Mount	No
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Ports	1
Surface Mount Compatible (SMC)	Yes

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

75783 Series

Use With

iPass Cable Assemblies, [79575](#) , [79576](#) ,
[74562](#) , [74563](#) , [79536](#) , [74573](#) ,

Temperature Range - Operating	-40° to +80°C
Termination Interface: Style	Surface Mount and Through Hole
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	0.5A
Grounding to Panel	None
Voltage - Maximum	30V AC (RMS)/DC
Solder Process Data	
Lead-freeProcess Capability	REFLOW
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-75783-001
Electrical Model Document	EE-75586-001
Packaging Specification	PK-75783-002
Product Specification	PS-75783-001-001
S-Parameter Model	SP-75586-001
Sales Drawing	SD-75783-001-001

This document was generated on 04/12/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75783-0311](#)